




REVISIONS					
REV	DATE	DESCRIPTION	BY	CHKD	APPD
Z	24JAN2018	REVISED PER ECO-12-007055	RS		MZ
AA	13FEB2020	REVISED PER ECO-20-002045	RK		MZ

RECOMMENDED PC BOARD LAYOUT

- 1

2

3

4
- HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED.

CONTACT MATERIAL: BRASS PER ASTM B36.

3.81um [.000150] MIN TIN OVER 2.54um [.000100] MIN COPPER.

0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.

.000150 MIN TIN OVER .000100 MIN CU, OR .000050 MIN NICKEL.

0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.

	6	NO	1-207121-0
	6	YES	207121-9
	5	YES	207121-8
OBSOLETE	4	NO	207121-4
OBSOLETE	4	YES	207121-3
OBSOLETE	3	NO	207121-2
OBSOLETE	3	YES	207121-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 03/12/92	TE Connectivity Ltd. PIN HEADER ASSEMBLY, 36 POSITION, METRIMATE	
DIMENSIONS: INCHES		CHK R.STONE 3-17-92		
		APVD A. TRAVIS 3-17-92		
		PRODUCT SPEC 108-10033		
MATERIAL		APPLICATION SPEC	SIZE	CAGE CODE
FINISH CONTACT: SEE TABLE		WEIGHT	DRAWING NO	RESTRICTED TO
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV AA