






LOC		DIST		REVISIONS				
P	LYR	DESCRIPTION		DATE	OWN	APVD		
	B	REVISED PER ECO-12-003566		11APR2012	KH	DD		



- △ MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0
TERMINALS: HIGH PERFORMANCE COPPER ALLOY
- △ FINISH:
30u" SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL
3. EACH SIGNAL WAFER CONTAINS 2 COLUMNS OF TERMINALS
- △ FINISH:
30u" SELECTIVE GOLD IN CONTACT AREA, SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL



SCALE 4:1



△ 4	2132423-5
△ 2	2132423-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN R. GRZYBOWSKI ZODEC2011	TE Connectivity	
DIMENSIONS:		CHK D. DIXON ZODEC2011	NAME IMAPCT, 3 PR., 6 COL., DAUGHTERCARD, RIGHT GUIDED SIGNAL MODULE, 0.39 EYELET, ORTHOGONAL	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. DIXON ZODEC2011	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
mm		PRODUCT SPEC	A100779C=2132423	
9 PLC ±0.25		APPLICATION SPEC	SCALE 6:1 SHEET 1 OF 1 REV B	
3 PLC ±0.15		WEIGHT		
5 PLC ±		CUSTOMER DRAWING		
4 PLC ±				
ANGLES FINISH				