



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	30AUG2019	SS	PS
	A1	REMOVED TOLERANCE FROM DIM F	18DEC2019	AY	PS

NOTES:


1. MATERIAL
HOUSING & P&P CAP : HIGH TEMPERATURE THERMOPLASTIC,
UL94-V0;COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH :
MATING SIDE : MIN. 0.76 µm GOLD OVER NICKEL UNDER PLATING.
SOLDER SIDE : MIN. 2.0 µm BRIGHT TIN OVER NICKEL UNDER PLATING.
2. PACKAGING: TUBE (WITH PICK AND PLACE CAP).
3. TOLERANCE NOT CUMULATIVE.
4. CUTTING BURR MAX. 0.25 mm





48.0	50.0	25	2-2842156-5
46.0	48.0	24	2-2842156-4
44.0	46.0	23	2-2842156-3
42.0	44.0	22	2-2842156-2
40.0	42.0	21	2-2842156-1
38.0	40.0	20	2-2842156-0
36.0	38.0	19	1-2842156-9
34.0	36.0	18	1-2842156-8
32.0	34.0	17	1-2842156-7
30.0	32.0	16	1-2842156-6
28.0	30.0	15	1-2842156-5
26.0	28.0	14	1-2842156-4
24.0	26.0	13	1-2842156-3
22.0	24.0	12	1-2842156-2
20.0	22.0	11	1-2842156-1
18.0	20.0	10	1-2842156-0
16.0	18.0	9	2842156-9
14.0	16.0	8	2842156-8
12.0	14.0	7	2842156-7
10.0	12.0	6	2842156-6
8.0	10.0	5	2842156-5
6.0	8.0	4	2842156-4
DIM "F"	DIM "E"	POS. PER ROW	TE PN


1-2842156-0 AS SHOWN

PICK AND PLACE CAP	3
CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUBHASREE S 07AUG2019	TE Connectivity			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK KARTHIK JK 13AUG2019	NAME AMPMODU 2mm BREAKAWAY HEADER, DUAL ROW, RIGHT ANGLE, 0.76 Au, TUBE, WITH PICK AND PLACE CAP			
	0 PLC ± 1 PLC ±0.2 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ±2°	APVD PRASHANTH S 14AUG2019				
	PRODUCT SPEC 108-64040					
	APPLICATION SPEC 114-32259					
MATERIAL SEE NOTES	FINISH SEE NOTES	WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C=2842156	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV A1	



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW /PIN-IN-PASTE