

13.4

7.5

5.48

1.0

13.88

2.8

6.7

(18.0)

(19.6)

10.45±0.25

14.15

2

1

5

4

3

HOUSING

RIGHT CONTACT

METAL CLIP

PLASTIC CLIP

LEFT CONTACT

(30.0)

3.9

4.0±0.3

8.75

13.7

NOTES, UNLESS OTHERWISE SPECIFIED:

1. MATERIAL:

HOUSING-THERMOPLASTIC GLASS PREINFORCED,
COLOR: BLACK,UL 94 V-0

CONTACT-COPPER ALLOY

2. AREA FOR DATE CODE AND P/N.

3. FINISH:

MATING AREA - NOBLE METAL OVERALL NICKEL

SOLD TYPE AREA - MATTE TIN OVERALL NICKEL.

4. SURFACE ROUGHNESS IN CONTACT AREA: Ra 1.6um MAX.

5. PLATING NOBLE MATERIAL ON FUNCTION AREA TO MEET THE CUSTOMER REQUIREMENT.

SCALE 2:1

PRODUCT VIEW

P/N:2204018-1

TOP INSULATION

SCALE 2:1

PRODUCT VIEW W/ TOP INSULATION

P/N:2204018-2

PRELIMINARY

2204018-2	DUAL CROWN CLIP JUNIOR CONN W/TOP INSULATION	2
2204018-1	DUAL CROWN CLIP JUNIOR CONN	1
PRODUCT NUMBER	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ±0.25

2 PLC ±0.15

3 PLC ±0.05

4 PLC ± -

ANGLES ±1°

FINISH

MATERIAL

-

DWN J.CHENG 11JAN2012

CHK S.ZHAO 11JAN2012

APVD S.ZHAO 11JAN2012

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

PLUGGABLE BUSBAR CONNECTOR
SOLDER VERSION
DUAL POLE CROWN CLIP JR

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=2204018

-

SCALE 4:1

SHEET 1 OF 2

REV A

1471-9 (3/11)

