





PANEL CUTOUT




NUT



3 = BRASS/NICKEL SHELL & NUT  
S = STAINLESS STEEL SHELL & NUT

1 = GOLD FLASH  
4 = 10 $\mu$ " GOLD



## NOTE:

## MATERIAL

HOUSING: PBT UL94V-0, BLACK  
CONTACT: BRASS  
NUT: BRASS  
SHELL: BRASS  
O-RING: EPDM

FINISH  
CONTACT:

GOLD PLATED  
OVER 50 $\mu$ " NICKEL  
NICKEL PLATED  
NICKEL PLATED

## ELECTRICAL

RATED CURRENT: 4A  
RATED VOLTAGE: 60V  
INSULATION RESISTANCE: 100 M $\Omega$ hms MIN.  
CONTACT RESISTANCE: 10 m $\Omega$ hms MAX.  
WATER PROOF: IP67  
ENVIRONMENT  
OPERATION TEMPERATURE: -40°C TO +85°C  
MAX WIRE AWG: 22

859-005-103R00Y

RoHS COMPLIANT

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: M. SIGMON DATE: 03-07-16

NorComp

SCALE: NTS SHEET 1 OF 1 REV 3

DWG NO. 859-005-103R00Y