




Original dimensions in mm [inch]

LC DUPLEX APC SINGLEMODE OPTICAL PLUG  
FOR Ø2.0 MM CABLE

Packaging  
1

Series  
LC

Issue  
14 FEB 11

Page  
2 / 2

Outer plug body : color GREEN

Monobloc

### GENERAL

- ❑ **TYPE** IEC 61754-20 (LC )  
Singlemode Zirconia ferrule  
RJ -45 latching connector system
- ❑ **FERRULE SIZE** 126 µm
- ❑ **FIBER SIZE** 9/125µm singlemode
- ❑ **CABLE SIZE & TYPE** Ø2,0 mm Duplex
- ❑ **CABLING PROCEDURE** Refer to 503.08.500 assembly instruction manual

### CHARACTERISTICS (Depending on fibre or cable construction)

- ❑ **OPTICAL** Attenuation at 1300 nm and 1550 nm  
Attenuation plug mated with reference plug : IEC 61300-3-4 Method B

| PARAMETER          | STD      |
|--------------------|----------|
| Mean               | ≤0.15 dB |
| Standard deviation | ≤0.1 dB  |

Attenuation of random mated connectors : IEC 61300-3-34

| PARAMETER          | STD       |
|--------------------|-----------|
| Mean               | ≤0.15 dB  |
| Standard deviation | ≤ 0.07 dB |

Return-Loss Maximum loss variation : IEC 61300-3-6

|     | RL      |
|-----|---------|
| APC | > 60 dB |

- ❑ **MECHANICAL**
  - Vibration test 10 to 55 Hz , 1,5 mm (peak to peak) , 2 Hr/axis
  - Impact test 1,5 m drop , 8 cycles
  - Mechanical Endurance 200 matings
  - Cable retention 68 N
- ❑ **ENVIRONMENTAL**
  - Storage temperature range -40 °C to +85 °C
  - Operating temperature range -40 °C to +85 °C
  - Thermal cycle test -40°C to +75°C , 21 Cycles , 168
  - Humidity/Condensation cycling test 95% RH , -10°C to +65°C , 14 cycles , 168 Hr

(Performance and specification : see document **GEN – F727 001**)