

## SPECIFICATIONS:

## MATERIALS:

HOUSING:	PA66, UL94 V-0, BLACK
CONTACT:	BRASS
NUT:	BRASS
SHELL:	BRASS
ORING:	EPDM

## FINISH:



CONTACT:	GOLD PLATED OVER NICKEL (SEE P/N KEY BELOW)
NUT:	NICKEL PLATED
SHELL:	NICKEL PLATED

## ELECTRICAL:

RATED CURRENT:	16A
RATED VOLTAGE:	63V
MAX WIRE AWG:	14

## ENVIRONMENT:

OPERATING TEMPERATURE:	-40°C TO 85°C
WATER PROOF:	IP67



RECOMMEND PANEL CUT-OUT

859-LP5-203R00Y

3 = BRASS/NICKEL SHELL & NUT  
 S = STAINLESS STEEL (SS) SHELL & NUT

1 = GOLD FLASH  
 4 = 10μ" GOLD

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
 THE PROPERTY OF NorComp AND SHALL NOT  
 BE REPRODUCED, COPIED OR USED AS THE  
 BASIS FOR THE MANUFACTURE OR SALE OF  
 APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
 J. KADEL

DATE:  
 08/01/2018

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	1	OF 1	REV 7
DWG NO. 859-LP5-203R00Y			