

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

2008

© COPYRIGHT 2008



TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC
IRDIST
-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	E12	1-964337-2 PACKAGING DETAILS HAS BEEN CHANGED	30MAY2017	SV	PKS
	E13	3-964337-2 REMOVED FROM GENERAL SALES	29JAN2020	JA	PKS



1 SLOT ACCEPTS SINGLE OR DOUBLE MAGNET WIRE
SAME DIAMETERS $\varnothing 0.18 \dots 0.265 \text{ mm}$
Kontakt geeignet fuer
Lackdraht $\varnothing 0.18 \dots 0.265 \text{ mm}$
(Einzeldraht oder zwei Draehle gleichen Durchmessers)

2 POKE IN TAB TERMINAL 3.4x0.5mm
Poke in Flachstecker 3.4x0.5mm

3 AREA WILL BE CUT BY TERMINATION
Bereich wird beim Kontaktieren abgetrennt

4 CAVITY ACCORDING TO TE SPEC. 411-18512
Kontakt Kammer nach TE Spec. 411-18512

5 IDENTIFICATION NO. FOR MAGNET WIRE RANGE (4)
Kennziffer fuer Lackdrahtbereich (4)

6 OVER THE MARKED LENGTH:
SELECTIVE Min. 0.4 μm GOLD OVER NI
Ueber die gekennzeichnete Laenge:
Selektiv Min. 0.4 μm Gold ueber Ni

7 REELED WITH PAPER INTERLAYER 0-737976-1
ON PLASTICREEL 1-725652-0
Reeling mit Papierzwischenlage 0-737976-1
auf Kunststoffspulen 1-725652-0

8 REELED WITH PAPER INTERLAYER 0-782504-1
ON PLASTICREEL 0-725652-4
Reeling mit Papierzwischenlage 0-782504-1
auf Kunststoffspulen 0-725652-4

9 QUANTITY 15000 PCS./REEL
Mengeneinheit 15000 stk./ spule


10 QUANTITY 10000 PCS./REEL
Mengeneinheit 10000 stk./ spule

11 REELED WITH PAPER INTERLAYER 782504-9
ON CARDBOARD REEL 1-973053-3
Reeling mit Papierzwischenlage 782504-9
auf Pappbandspule 1-973053-3

12 REELED WITH PAPER INTERLAYER 1-782504-1
ON PLASTIC REEL 1-973162-3
Reeling mit Papierzwischenlage 1-782504-1
auf Kunststoffspulen 1-973162-3

	3-964337-7 	A	-	CuNiSi	FLASH GOLD OVER NICKEL
	 2-964337-7 	B	-	CuNiSi	FLASH GOLD OVER NICKEL
	2-964337-2 	A	-	CuNiSi	TIN PLATED
SUPERSEDED BY PN 2-964337-7	1-964337-7 	A	-	CuNiSi	 FLASH GOLD OVER Ni
	 1-964337-2 	C	-	CuNiSi	PRE TINNED
SUPERSEDED BY PN 2-964337-7	964337-7 	B	-	CuNiSi	 FLASH GOLD OVER Ni
	964337-3 	C	-	CuZn	PRE TINNED
	964337-2 	C	-	CuNiSi	PRE TINNED
	964337-1 	B	-	CuNiSi	BLANK
NOTE	PART NO	REV.	PCS.	MATERIAL	SURFACE COLOUR

DIRECTION OFF TOP OF REEL



Spec. 107-3 Fig. 272

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN Rudolph 15-03-95

CHK H. Plöcker 20-03-95

APVD -

PRODUCT SPEC

108-2012

APPLICATION SPEC


114-2046

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS:

mm



MATERIAL

SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
n. ISO 8015, n. ISO 2768-
n. DIN 16901 - 140

0 PLC $\pm 0.2 \text{ mm}$
1 PLC $\pm 0.2 \text{ mm}$
2 PLC $\pm -$
3 PLC $\pm -$
4 PLC $\pm -$
ANGLES $\pm 1^\circ$

FINISH

SEE TABLE

TE

TE Connectivity

NAME

MAG MATE LEAF TERMINAL
MARK II

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-964337

RESTRICTED TO

-

SCALE 10:1

SHEET 1 OF 1

REV E13