

Actuator

45-
2819.4D50.003



<https://eao.com/p/45-2819.4D50.003>

Your product:



45-2819.4D50.003 Actuator

FRONT

Front dimension:	Ø 38 mm
Front bezel colour:	Sand grey
Front bezel material:	Metal

MOUNTING

Design:	flush
---------	-------

OPERATING-/INDICATION PART

Lever colour:	Green
Lever shape:	long
Lever material:	plastic

MECHANICAL CHARACTERISTIC

Weight:	0.084 kg
Switching action:	Maintained - Rest - Maintained
Switching positions:	3 positions
Switching angle:	45° left / 45° right
Mechanical lifetime:	1 Mio. cycles of operation
Operating frequency:	1 800/h


AMBIENT CONDITION

IP front protection:	IP66, IP67, IP69K
----------------------	-------------------


Operating temperature:	– 25 °C ... + 70 °C
Storage temperature:	– 40 °C ... + 80 °C
Climate resistance:	During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6
Vibration resistance:	According to IEC 60068-2-6: 10 ... 500 Hz: 5 g
Shock resistance:	According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms

OTHER

Housing material:	Metal
Hints:	Front panel thickness 1 ... 6 mm
Short Description:	Actuator, Ø 38 mm, optional illuminative, Green, long, Sand grey, Metal, Maintained - Rest - Maintained, IP66, IP67, IP69K
Switching positions:	



Wiring diagrams:



Dimension drawings:

