

## SCZ 3.81/12/180F SN OR BX

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Product image



The inverted SCZ pin plug with clamping-yoke screw connection is designed for straight wire connections in 3.81-mm pitch. It can be used in two ways:

- for wire-to-wire connections together with the BCZ
- as a mating plug for the touch-safe BCL socket block on the PCB.

The SCZ is available in four different versions:

- Without flange ("G", closed)
- With standard flange ("F", with socket nut)
- With inverted flange ("FI", with screw)
- and with Weidmüller's patented release latch for a tool-free, no-strain disconnect

The SCZ provides space for labelling and can be coded.

### General ordering data

|              |                                                                                                                                    |
|--------------|------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, male plug, 3.81 mm, Number of poles: 12, 180°, Clamping yoke connection, Clamping range, max.: 1.5 mm², Box |
| Order No.    | <a href="#">1971020000</a>                                                                                                         |
| Type         | SCZ 3.81/12/180F SN OR BX                                                                                                          |
| GTIN (EAN)   | 4032248680832                                                                                                                      |
| Qty.         | 50 pc(s).                                                                                                                          |
| Product data | IEC: 320 V / 17.5 A / 0.2 - 1.5 mm²<br>UL: 300 V / 10 A / AWG 28 - AWG 16                                                          |
| Packaging    | Box                                                                                                                                |

Creation date September 17, 2022 8:53:50 PM CEST

## SCZ 3.81/12/180F SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 18.4 mm | Depth (inches)  | 0.724 inch |
| Height     | 11.1 mm | Height (inches) | 0.437 inch |
| Net weight | 11.22 g |                 |            |

## Environmental Product Compliance

|            |                |      |                                      |
|------------|----------------|------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 | SCIP | cec56c8c-fe86-40ec-b01a-e8e288a878ac |
|------------|----------------|------|--------------------------------------|

## System Parameters

|                                              |                                     |                   |              |
|----------------------------------------------|-------------------------------------|-------------------|--------------|
| Product family                               | OMNIMATE Signal - series BC/SC 3.81 |                   |              |
| Type of connection                           | Field connection                    |                   |              |
| Wire connection method                       | Clamping yoke connection            |                   |              |
| Pitch in mm (P)                              | 3.81 mm                             |                   |              |
| Pitch in inches (P)                          | 0.15 inch                           |                   |              |
| Conductor outlet direction                   | 180°                                |                   |              |
| Number of poles                              | 12                                  |                   |              |
| L1 in mm                                     | 41.91 mm                            |                   |              |
| L1 in inches                                 | 1.65 inch                           |                   |              |
| Number of rows                               | 1                                   |                   |              |
| Pin series quantity                          | 1                                   |                   |              |
| Rated cross-section                          | 1 mm <sup>2</sup>                   |                   |              |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch              |                   |              |
| Touch-safe protection acc. to DIN VDE 0470   | IP 20                               |                   |              |
| Volume resistance                            | ≤5 mΩ                               |                   |              |
| Can be coded                                 | Yes                                 |                   |              |
| Stripping length                             | 7 mm                                |                   |              |
| Clamping screw                               | M 2                                 |                   |              |
| Screwdriver blade                            | 0.4 x 2.5                           |                   |              |
| Screwdriver blade standard                   | DIN 5264-A                          |                   |              |
| Plugging cycles                              | 25                                  |                   |              |
| Plugging force/pole, max.                    | 8 N                                 |                   |              |
| Pulling force/pole, max.                     | 5 N                                 |                   |              |
| Tightening torque                            | Torque type                         | Wire connection   |              |
|                                              | Usage information                   | Tightening torque | min. 0.2 Nm  |
|                                              |                                     |                   | max. 0.25 Nm |
|                                              | Torque type                         | Screw flange      |              |
|                                              | Usage information                   | Tightening torque | min. 0.15 Nm |
|                                              |                                     |                   | max. 0.2 Nm  |

## Material data

|                                       |              |                                       |        |
|---------------------------------------|--------------|---------------------------------------|--------|
| Insulating material                   | PA 66 GF 30  | Colour                                | orange |
| Colour chart (similar)                | RAL 2000     | Insulating material group             | II     |
| Comparative Tracking Index (CTI)      | ≥ 550        | UL 94 flammability rating             | V-0    |
| Contact material                      | Copper alloy | Contact surface                       | tinned |
| Layer structure of plug contact       | 4...8 µm Sn  | Storage temperature, min.             | -40 °C |
| Storage temperature, max.             | 70 °C        | Operating temperature, min.           | -50 °C |
| Operating temperature, max.           | 120 °C       | Temperature range, installation, min. | -25 °C |
| Temperature range, installation, max. | 120 °C       |                                       |        |

## SCZ 3.81/12/180F SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors suitable for connection

|                                                                     |                                        |                              |                         |              |
|---------------------------------------------------------------------|----------------------------------------|------------------------------|-------------------------|--------------|
| Clamping range, min.                                                | 0.08 mm <sup>2</sup>                   |                              |                         |              |
| Clamping range, max.                                                | 1.5 mm <sup>2</sup>                    |                              |                         |              |
| Wire connection cross section AWG, min.                             | AWG 28                                 |                              |                         |              |
| Wire connection cross section AWG, max.                             | AWG 16                                 |                              |                         |              |
| Solid, min. H05(07) V-U                                             | 0.2 mm <sup>2</sup>                    |                              |                         |              |
| Solid, max. H05(07) V-U                                             | 1.5 mm <sup>2</sup>                    |                              |                         |              |
| Flexible, min. H05(07) V-K                                          | 0.2 mm <sup>2</sup>                    |                              |                         |              |
| Flexible, max. H05(07) V-K                                          | 1.5 mm <sup>2</sup>                    |                              |                         |              |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm <sup>2</sup> min. |                                        |                              |                         |              |
| w. plastic collar ferrule, DIN 46228 pt 4, 1.5 mm <sup>2</sup> max. |                                        |                              |                         |              |
| w. wire end ferrule, DIN 46228 pt 1, min.                           | 0.2 mm <sup>2</sup>                    |                              |                         |              |
| w. wire end ferrule, DIN 46228 pt 1, max.                           | 1.5 mm <sup>2</sup>                    |                              |                         |              |
| Plug gauge in accordance with EN 60999 a x b; ø                     | 2.4 mm x 1.5 mm ; 2.4 mm               |                              |                         |              |
| Clampable conductor                                                 | Cross-section for conductor connection | Type                         | fine-wired              |              |
|                                                                     |                                        | nominal                      | 0.5 mm <sup>2</sup>     |              |
|                                                                     |                                        | wire end ferrule             | Stripping length        | nominal 6 mm |
|                                                                     |                                        | Recommended wire-end ferrule | <a href="#">H0.5/6</a>  |              |
|                                                                     | Cross-section for conductor connection | Type                         | fine-wired              |              |
|                                                                     |                                        | nominal                      | 0.75 mm <sup>2</sup>    |              |
|                                                                     |                                        | wire end ferrule             | Stripping length        | nominal 6 mm |
|                                                                     |                                        | Recommended wire-end ferrule | <a href="#">H0.75/6</a> |              |
|                                                                     | Cross-section for conductor connection | Type                         | fine-wired              |              |
|                                                                     |                                        | nominal                      | 1 mm <sup>2</sup>       |              |
|                                                                     |                                        | wire end ferrule             | Stripping length        | nominal 6 mm |
|                                                                     |                                        | Recommended wire-end ferrule | <a href="#">H1.0/6</a>  |              |
|                                                                     | Cross-section for conductor connection | Type                         | fine-wired              |              |
|                                                                     |                                        | nominal                      | 1.5 mm <sup>2</sup>     |              |
|                                                                     |                                        | wire end ferrule             | Stripping length        | nominal 7 mm |
|                                                                     |                                        | Recommended wire-end ferrule | <a href="#">H1.5/7</a>  |              |

Reference text The outside diameter of the plastic collar should not be larger than the pitch (P). Length of ferrules is to be chosen depending on the product and the rated voltage.

## Rated data acc. to IEC

|                                                                           |                        |                                                                       |                  |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 17.5 A           |
| Rated current, max. number of poles (Tu=20°C)                             | 17.1 A                 | Rated current, min. number of poles (Tu=40°C)                         | 17.5 A           |
| Rated current, max. number of poles (Tu=40°C)                             | 15.2 A                 | Rated voltage for surge voltage class / pollution degree II/2         | 320 V            |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 160 V            |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV                 | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV           |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV                 | Short-time withstand current resistance                               | 3 x 1s with 76 A |

## SCZ 3.81/12/180F SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Rated data acc. to CSA

Institute (CSA)



Certificate No. (CSA)

200039-1121690

Rated voltage (Use group B / CSA) 300 V

Rated voltage (Use group C / CSA) 50 V

Rated current (Use group B / CSA) 11 A

Rated current (Use group C / CSA) 11 A

Wire cross-section, AWG, min. AWG 28

Wire cross-section, AWG, max. AWG 16

Reference to approval values  
Specifications are maximum values, details - see approval certificate.

## Packing

Packaging Box

VPE length 292 mm

VPE width 115 mm

VPE height 25 mm

## Type tests

Test: Durability of markings

Standard

DIN EN 61984 section 7.3.2 / 09.02 taking pattern from DIN EN 60068-2-70 / 07.96

Test

mark of origin, type identification, rated voltage, rated cross-section, pitch, type of material, approval marking UL, approval marking CSA

Evaluation

available

Test

durability

Evaluation

passed

Test: Misengagement (Non-interchangeability)

Standard

DIN EN 61984 section 6.3 and 6.9.1 / 09.02, DIN EN 60512-13-5 / 11.06

Test

180° turned without coding elements

Evaluation

passed

Test

visual examination

Evaluation

passed

## SCZ 3.81/12/180F SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|                                                           |                |                                                                                    |                               |
|-----------------------------------------------------------|----------------|------------------------------------------------------------------------------------|-------------------------------|
| Test: Clampable cross section                             | Standard       | DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 12.02 |                               |
|                                                           | Conductor type | Type of conductor and conductor cross-section                                      | solid 0.08 mm <sup>2</sup>    |
|                                                           |                | Type of conductor and conductor cross-section                                      | stranded 0.08 mm <sup>2</sup> |
|                                                           |                | Type of conductor and conductor cross-section                                      | solid 1.5 mm <sup>2</sup>     |
|                                                           |                | Type of conductor and conductor cross-section                                      | stranded 1.5 mm <sup>2</sup>  |
|                                                           |                | Type of conductor and conductor cross-section                                      | AWG 28/1                      |
|                                                           |                | Type of conductor and conductor cross-section                                      | AWG 28/19                     |
|                                                           |                | Type of conductor and conductor cross-section                                      | AWG 16/1                      |
|                                                           |                | Type of conductor and conductor cross-section                                      | AWG 16/19                     |
|                                                           | Evaluation     | passed                                                                             |                               |
| Test for damage to and accidental loosening of conductors | Standard       | DIN EN 60999-1 section 9.4 / 12.00                                                 |                               |
|                                                           | Requirement    | 0.2 kg                                                                             |                               |
|                                                           | Conductor type | Type of conductor and conductor cross-section                                      | stranded 0.25 mm <sup>2</sup> |
|                                                           |                | Type of conductor and conductor cross-section                                      | AWG 28/1                      |
|                                                           |                | Type of conductor and conductor cross-section                                      | AWG 28/19                     |
|                                                           | Evaluation     | passed                                                                             |                               |
|                                                           | Requirement    | 0.3 kg                                                                             |                               |
|                                                           | Conductor type | Type of conductor and conductor cross-section                                      | solid 0.5 mm <sup>2</sup>     |
|                                                           |                |                                                                                    |                               |
|                                                           | Evaluation     | passed                                                                             |                               |
|                                                           | Requirement    | 0.4 kg                                                                             |                               |
|                                                           | Conductor type | Type of conductor and conductor cross-section                                      | solid 1.5 mm <sup>2</sup>     |
|                                                           |                | Type of conductor and conductor cross-section                                      | stranded 1.5 mm <sup>2</sup>  |
|                                                           |                | Type of conductor and conductor cross-section                                      | AWG 16/1                      |
|                                                           |                | Type of conductor and conductor cross-section                                      | AWG 16/19                     |
|                                                           | Evaluation     | passed                                                                             |                               |

## SCZ 3.81/12/180F SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|               |                |                                               |                               |
|---------------|----------------|-----------------------------------------------|-------------------------------|
| Pull-out test | Standard       | DIN EN 60999-1 section 9.5 / 12.00            |                               |
|               | Requirement    | ≥10 N                                         |                               |
|               | Conductor type | Type of conductor and conductor cross-section | stranded 0.25 mm <sup>2</sup> |
|               |                | Type of conductor and conductor cross-section | AWG 28/1                      |
|               |                | Type of conductor and conductor cross-section | AWG 28/19                     |
|               | Evaluation     | passed                                        |                               |
|               | Requirement    | ≥20 N                                         |                               |
|               | Conductor type | Type of conductor and conductor cross-section | H05V-U0.5                     |
|               |                | passed                                        |                               |
|               |                | ≥40 N                                         |                               |
|               | Conductor type | Type of conductor and conductor cross-section | H07V-U1.5                     |
|               |                | Type of conductor and conductor cross-section | H07V-K1.5                     |
|               |                | Type of conductor and conductor cross-section | AWG 16/1                      |
|               |                | Type of conductor and conductor cross-section | AWG 16/19                     |
|               | Evaluation     | passed                                        |                               |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002638    | ETIM 7.0    | EC002638    |
| ETIM 8.0    | EC002638    | ECLASS 9.0  | 27-44-03-09 |
| ECLASS 9.1  | 27-44-03-09 | ECLASS 10.0 | 27-44-03-09 |
| ECLASS 11.0 | 27-46-02-02 | ECLASS 12.0 | 27-46-02-02 |

## Important note

|                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
|----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                                                                                                                                                                                                                    |
| Notes          | <ul style="list-style-type: none"> <li>• Additional variants on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• Wire end ferrule with plastic collar to DIN 46228/4</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• Long term storage of the product with average temperature of 50 °C and average humidity 70%, 36 months</li> </ul> |

## SCZ 3.81/12/180F SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search UL Website

Certificate No. (cURus) E60693

## Downloads

Approval/Certificate/Document of  
Conformity [Declaration of the Manufacturer](#)Engineering Data [CAD data – STEP](#)Catalogues [Catalogues in PDF-format](#)Brochures [FL DRIVES EN](#)  
[MB DEVICE MANUF. EN](#)  
[FL DRIVES DE](#)  
[FL BUILDING SAFETY EN](#)  
[FL APPL LED LIGHTING EN](#)  
[FL INDUSTR.CONTROLS EN](#)  
[FL MACHINE SAFETY EN](#)  
[FL HEATING ELECTR EN](#)  
[FL APPL INVERTER EN](#)  
[FL BASE STATION EN](#)  
[FL ELEVATOR EN](#)  
[FL POWER SUPPLY EN](#)  
[FL 72H SAMPLE SER EN](#)  
[PO OMNIMATE EN](#)  
[PO OMNIMATE EN](#)


## SCZ 3.81/12/180F SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Product image



### Dimensional drawing



### Graph



### Graph



### Graph



WEITERGABE SOWIE Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.  
Zuweihandlungen Verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksmustererhaltung vorbehalten.  
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.  
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. ALL RIGHTS RESERVED IN THE EVENT OF THE GRANT OF A PATENT, UTILITY MODEL OR DESIGN.

SCZ 3.81/.../180G ...



SCZ 3.81/.../180FI ...



SCZ 3.81/.../180F ...



SCZ 3.81/.../180LR ...



KUNDENZEICHNUNG  
CUSTOMER DRAWING

For the mounting of PCBs, it should be noted that the rated data stated here relates only to the PCB components alone.  
The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 664 / VDE 0110.  
The current- carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller PCB components are tested to the DIN EN 61984 standard, and are valid for its field of application.  
Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

|                |  |                          |            |                                                                                               |                    |  |
|----------------|--|--------------------------|------------|-----------------------------------------------------------------------------------------------|--------------------|--|
|                |  | 55304/5<br>03.06.11 GE_G |            | 00                                                                                            | CAT.NO.: . . . . . |  |
| MODIFICATION   |  | <b>Weidmüller</b>        |            | 2 40408 05                                                                                    |                    |  |
| DRAWN          |  | DATE                     | NAME       | DRAWING NO. SHEET . OF . SHEETS                                                               |                    |  |
| RESPONSIBLE    |  | 09.10.2008               | SHI_S      |                                                                                               |                    |  |
| SUPERSEDES:    |  | CHECKED                  | 03.06.2011 | ISSUE NO.                                                                                     |                    |  |
| SUPERSEDED BY: |  | APPROVED                 | XU_S       | 7078                                                                                          |                    |  |
| SCALE: 2/1     |  | Richter_G                |            | SCZ 3.81/.../180...<br>ZUGBUEGELANSCHLUSS STIFTELEISTE<br>CLAMPING YOKE CONNECTION PIN HEADER |                    |  |
|                |  | PRODUCT FILE: SCZ 3.81   |            |                                                                                               |                    |  |