

Actuator

71-651.0



<https://eao.com/p/71-651.0>

Your product:



71-651.0

Actuator

OPERATING-/INDICATION PART

Lever shape:	short
Lever material:	plastic

ELECTRICAL CHARACTERISTICS

Surge voltage resistance:	2500 VAC, 50 Hz, 1 minute, as per DIN / IEC 60512-2 between all terminals and earth		
Switching voltage and switching current:	Switch rating AC cosφ 0,7 ... 0,8 gemäss EN IEC 60947-5-1		
	Voltage	250 VAC	
	Current	3 A	
	Switch rating DC gemäss EN IEC 60947-5-1		
	Voltage	24 VDC	250 VDC
	Current	3 A	0.5 A
Recommended minimum operational data:	Voltage	5 VAC/DC	
	Current	10 mA	

MECHANICAL CHARACTERISTIC

Mechanical lifetime:	100 000 cycles of operation
Switching angle:	42° left / 42° right
Switching positions:	3 positions
Switching system:	Self-cleaning, double-break snap action switching system, 1 normally closed and 1 normally open contact per element.
Weight:	0.003 kg
Switching action:	Momentary - Rest - Momentary
Tightening torque:	Fixing nut max. 0.5 Nm

AMBIENT CONDITION

Storage temperature:	– 40 °C ... + 85 °C
IP Protection:	IP65 front side
Vibration resistance:	Max. 100 m / s ² from 10 Hz ... 500 Hz, (sinusoidal EN IEC 60068-2-6)
Climate resistance:	Damp heat, steady: 56 days, + 40 °C/93 % relative humidity, according to EN IEC 60068-2-78
Shock resistance:	Max. 500 m/s ² , pulse width, 3-axis (sinusoidal EN IEC 60068-2-27)
Operating temperature:	– 25 °C ... + 55 °C

CERTIFICATE

Conformities:	CE, UKCA, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)
----------------------	---



OTHER

Short Description:	Actuator, optional illuminative, short, Momentary - Rest - Momentary
---------------------------	--


Hints:	Pitch of the front plate mounting holes must agree with the printed circuit board holes Ø 3.5 mm
---------------	--

Housing material:	Plastic, according to UL 94 V0
--------------------------	--------------------------------



Dimension drawings:



Switching positions:



Mounting cut-outs:



Wiring diagrams:

