





DRAWING FOR REFERENCE: This is subject to change without notice
08/11/2012




MATING FIGURE




- NOTES
1. LEAD CO-PLANARITY SHALL BE 0.10mm MAX.
 2. UNMATING SHALL BE DONE WITH THE SPECIFIC EXTRACTION TOOL.

A-A(FREE)




B-B(FREE)



2	LCP	UL94V-0 , BLACK	6	PS	BLACK
1	PHOSPHOR BRONZE	CONTACT AREA : Au PLATING 0.3μm min LEAD AREA : Au PLATING 0.1μm min UNDER PLATING : Ni PLATING 2μm min	5	POLYESTER	CLEAR
NO.	MATERIAL	FINISH , REMARKS	4	PS	CLEAR
			3	PHOSPHOR BRONZE	WHOLE AREA : Au PLATING 0.1μm min UNDER PLATING : Ni PLATING 2μm min
UNITS	mm	SCALE	5 : 1	COUNT	1
		DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
		APPROVED : TS. SAKATA	11.10.21		
		CHECED : IO. DENPOUYA	11.10.21		
		DESIGNED : TP. MATSUMOTO	11.10.21		
		DRAWN : YK. NAKATSU	09.03.27		
		DRAWING NO.	EDC3-316102-01		
		PART NO.	DF36J-25S-0.4V(51)		
		CODE NO.	CL662-4023-3-51		

DRAWING FOR REFERENCE: This is subject to change without notice
08/11/2012



DETAIL OF PART No. LABEL

生産月日	年 月 日
製品コード	CL662-4023-3-51
製品名	DF36J-25S-0.4V(51)
納入数量	500pcs
納入者	ヒロセ電機(株)

SUPPLIER
QUANTITY
PART No.
CODE No.
DATE OF MANUFACTURED

RECOMMENDED PATTERN(5:1)

RECOMMENDED METAL MASK

THICKNESS: 0.15mm
OPENING RATIO: LEAD AREA 90%
GROUND AREA 90%

NOTES 3. PER REEL: 500 COMPONENTS
4. REFER TO JIS C 0806. (PACKAGING OF COMPONENTS FOR AUTOMATIC HANDLING)
5. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

DRAWING NO.	EDC3-316102-01
PART NO.	DF36J-25S-0.4V(51)
CODE NO.	CL662-4023-3-51

2/2