



Jun.1.2019 Copyright 2019 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



NOTES 1 Rotation examples of ref. No. ① and No. ⑦ are shown.
2 The recommended clamp torque of ref. No. ⑩ : 0.2 to 0.3N・m.
3 Across flats of hexagon hole of ref. No. ⑩ : 1.27

			10	CHLOROPRENE RUBBER	(BLACK)					
5	PHOSPHOR BRONZE	NICKEL PLATING	9	STEEL	NICKEL PLATING JIS B 1177 HEXAGON SOCKET SET SCREW M2.6X0.45X2					
4	PHENOL FORMALDEHYDE	(BLACK) UL94V-0	8	BRASS	NICKEL PLATING JIS B 1111 PAN HEAD MACHINE SCREW M3X0.5X8					
3	PHENOL FORMALDEHYDE	(BLACK) UL94V-0	7	POLYACETAL						
2	COPPER ALLOY	SILVER PLATING 3μ min.	6	ALUMINUM ALLOY	MATTE FINISH NICKEL PLATED					
1	ALUMINUM ALLOY	NICKEL PLATING	5	ALUMINUM ALLOY	MATTE FINISH NICKEL PLATED					
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS				
UNITS mm				SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED		HY. KOBAYASHI	15.09.14	DRAWING NO. EDC-119151-00-00				
		CHECKED		HY. KOBAYASHI	15.09.14	PART NO. JRC16BP-10PA				
		DESIGNED		KN. IKEHARA	15.09.14	CODE NO. CL114-0300-0-00				
		DRAWN		KN. IKEHARA	15.09.14					
5		6		7		8				