

SUMMARY

Wires

Low voltage **19**



Image is for illustrative purpose only

Series	2P
Termination type	Male crimp
IP rating	66
AWG wire size	30.00 - 22.00
Cable Ø	7.30 - 9.20 mm
Status	active
Matching parts	CNB.M19.GYMR

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	CF*: Straight plug with cable collet, watertight (IP 66) and nut for fitting a bend relief
Keying	3 keys (alpha=0, gamma=60; Plug: male contacts; Receptacle: female contacts)
Housing Material	PSU (Polysulfone), gray
Weight	11.48 g

Performance

Configuration	2P.M19 : 19 Low V.
Insulator	Y: PEEK for crimp contacts
Rated Current	5 Amps

Specifications

Test voltage (kV rms) Contact-contact: 1.4
 Air clearance min.: 0.6 mm
 Creepage distance min.: 0.6 mm

Others




Endurance (Shell): >1000 mating cycles
 Temp (min / max): -50°C / +150°C
 F ret (min): 150 N

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

F ret (max): 250 N

Steam sterilization: 20 times (with potting on rear connection)

DRAWINGS



RECOMMENDED BY LEMO

Tools

Crimp Tool: [DPC.91.701.V](#)

Crimp settings: AWG/Selector = 22-24-26/6-5-5

Positionner: [DCE.91.072.BVC](#)

Replacement contact: FGG.2B.555.ZZC

Cables

CMN.19.T22.079QGZE	TPR (medical)	Grey	
--------------------	---------------	------	--

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.