




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
D		REVISED PER ECO-15-017922	09APR2016	AP	RP
E		REVISED PER ECR-19-011161	14JAN2020	IT	SH



2007538-5 AS SHOWN



- ⚠ MATERIALS:
CAGE ASSEMBLY- NICKEL SILVER ALLOY PER ASTM B 122.
BRACKET- STAINLESS STEEL.
EMI GASKET- PLATED FILLED SILICONE.
HOUSING- BLACK LCP, UL 94V-0 RATED.
CHICKLET- BLACK LCP, UL 94V-0 RATED.
LIGHT PIPE- POLYCARBONATE, CLEAR.
INSERT - (FOR LIGHT PIPE PART NUMBERS ONLY) - LCP, BLACK, UL 94V-0.
CONTACT- COPPER ALLOY.

- ⚠ DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.

3. MINIMUM PCB THICKNESS OF 1.5.

- ⚠ CONTACT FINISH- CONFORMS TO THE REQUIREMENTS OF TYCO ELECTRONICS PRODUCT SPECIFICATION 108-2331, BASED ON EIA/ECA-364-1000.01A, (CONTROLLED ENVIRONMENT APPLICATIONS) ON MATING INTERFACE, TIN-LEAD ON NEEDLE EYE.

- ⚠ CONTACT FINISH- CONFORMS TO THE REQUIREMENTS OF TYCO ELECTRONICS PRODUCT SPECIFICATION 108-2331, BASED ON EIA/ECA-364-1000.01A, (CONTROLLED ENVIRONMENT APPLICATIONS) ON MATING INTERFACE, TIN ON NEEDLE EYE.

- ⚠ FOR HOLE SIZE AND PLATINGS, SEE APPLICATION SPEC 114-13219.

- ⚠ THE ENTIRE AREA OF THE CONNECTOR FOOTPRINT, INDICATED BY THE DASHED LINE, TO BE CONSIDERED THE KEEPOUT AREA FOR COMPONENTS AND SIGNAL TRACES, TOP SIDE ONLY. TOP SIDE TRACES ALLOWED WITHIN CONNECTOR HOLE PATTERN.


- ⚠ LIGHT PIPE PAD LAYOUT IS FOR 0805 LOW PROFILE LED PACKAGE WITH A HEIGHT OF 0.8mm.

- ⚠ ADDITIONAL COMPONENT LOCATED WITHIN LATCHPLATE FOR EMI SUPPRESSION.


	YES 		NO LIGHT PIPES	1-2007538-8
			OUTER 2 LIGHT PIPES	1-2007538-7
			INNER 2 LIGHT PIPES	1-2007538-6
			4 LIGHT PIPES	1-2007538-5
	NO		NO LIGHT PIPES	2007538-8
			OUTER 2 LIGHT PIPES	2007538-7
			INNER 2 LIGHT PIPES	2007538-6
			4 LIGHT PIPES	2007538-5
SUPERSEDED	NO		NO LIGHT PIPES	2007538-4
			OUTER 2 LIGHT PIPES	2007538-3
			INNER 2 LIGHT PIPES	2007538-2
			4 LIGHT PIPES	2007538-1
	ENHANCED EMI	FINISH	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SHIRK 03JAN2007	TE TE Connectivity	
DIMENSIONS:		CHK D. SZCZESNY 03JAN2007		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. SZCZESNY 03JAN2007	NAME CAGE AND PT CONNECTOR ASSEMBLY, WITH EMI GASKET, PRESS FIT, 2X1, STACKED SFP+	
	0 PLC ±0.10	PRODUCT SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
	1 PLC ±0.10	108-2331		
	2 PLC ±0.10	APPLICATION SPEC	A100779C=2007538	
	3 PLC ±0.10	114-13219		
MATERIAL	FINISH	WEIGHT	SCALE 5:1 SHEET 1 OF 4 REV E	
⚠1	⚠4 ⚠5	CUSTOMER DRAWING		


REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-




2007538-5 AND 1-2007538-5
SCALE 3:1






2007538-6 AND 1-2007538-6
SCALE 3:1




2007538-7 AND 1-2007538-7
SCALE 3:1




2007538-8 AND 1-2007538-8
SCALE 3:1


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SHIRK	03JAN2007	 TE Connectivity				
		CHK D. SZCZESNY	03JAN2007					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	CAGE AND PT CONNECTOR ASSEMBLY, WITH EMI GASKET, PRESS FIT, 2X1, STACKED SFP+			
		0 PLC	±0.10			PRODUCT SPEC		
		1 PLC	±0.10	108-2331	SIZE A100779	CAGE CODE C=2007538	DRAWING NO =2007538	RESTRICTED TO -
		2 PLC	±0.10	APPLICATION SPEC				
		3 PLC	±0.10	114-13219				
		4 PLC	±	WEIGHT				
MATERIAL		FINISH	CUSTOMER DRAWING	SCALE 5:1		SHEET 1 OF 4		REV E



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



DETAIL G
CONNECTOR HOUSING
KEEPOUT ZONE
SCALE 10:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SHIRK	03JAN2007	 TE Connectivity	
		CHK D. SZCZESNY	03JAN2007		
DIMENSIONS:		APVD D. SZCZESNY	03JAN2007	NAME CAGE AND PT CONNECTOR ASSEMBLY, WITH EMI GASKET, PRESS FIT, 2X1, STACKED SFP+	
mm		PRODUCT SPEC			
		108-2331		SIZE A1	
		APPLICATION SPEC			
		114-13219		CAGE CODE 00779	
		FINISH			
MATERIAL		WEIGHT		CUSTOMER DRAWING	
		SCALE 5:1		SHEET 1 OF 4	
				REV E	