

S40B0C-P04MFG0-350S  
series\_b, type\_s4



General information

|                   |                     |
|-------------------|---------------------|
| Part number       | S40B0C-P04MFG0-350S |
| Termination       | solder              |
| Size              | 0                   |
| Locking principle | push                |
| Coding            | 0_key               |
| Cable Diameter    | cable_mini_35       |
| Cable outlet      | bend_relief         |



Illustrations may differ from original product.  
Dimensions, unless otherwise specified, in mm.

**CODING:** 0 °

**POSITIONS:** 4 Positions

**DIMENSIONS:**

The pin layout corresponds to the view on the termination area

Contact insert description

|                      |              |
|----------------------|--------------|
| Number of contacts   | 4            |
| Contact type         | pins         |
| Contact diameter     | 07mm         |
| Insulator material   | peek         |
| Wire cross section   | 22_awg       |
| Termination          | solder       |
| Termination diameter | 085mm        |
| Data transmission    | ethernet_100 |

reverse\_gender\_on\_request

Technical information

|                                          |          |               |
|------------------------------------------|----------|---------------|
| Max. creepage and air clearance distance | 06_mm    | 08_mm         |
| Nominal current single contact           | 075_a    | iec_60512_5_2 |
| Nominal current insert                   | 7,5 A    | vde_0298_4    |
| Test voltage                             | 09_kv_ac | sae_13441     |

safety\_text

Mechanical and environmental data

|                       |          |
|-----------------------|----------|
| Degree of protection* | ip68     |
| Operating temperature | 40_120_c |
| Mating cycles         | 5000     |

mated

Material and surface treatments

|         |               |
|---------|---------------|
| Housing | m_chrome      |
| Contact | cu_alloy_gold |

safety\_text\_2  
data\_text  
ul\_text  
illustrative\_text