

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	R2	REVISED PER ECO-17-006294	09OCT2017	RS	DR
	R3	REVISED PER ECO-19-010628	12FEB2020	RK	DR


- 1 FOR $\varnothing 7.925$ [$\varnothing .312$] MAX WIRE INSULATION.
- 2 NOTE DELETED.
- 3

MATERIAL: BODY; COPPER PER ASTM B152
INSULATION; PVC
- 4

FINISH: BODY; TIN PLATE 0.00254[.000100]
MIN EXT. THK. PER ASTM B-545
INSULATION; COLOR-PURPLE

 WIRE RANGE	 Listed	 LR7189 Certified
22-10 AWG SOLID OR STRANDED	22-10 AWG SOLID OR STRANDED	22-10 AWG SOLID OR STRANDED

STAMPING DETAIL



1,500	TAPE MOUNTED	1-36965-1
500	LOOSE PIECE	36965
QTY	DESCRIPTION	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142


MAX RECOMMENDED OPERATING
TEMPERATURE:
90°C[194°F] MAX

VOLTAGE RATING:
300V MAX

CIRCULAR MIL AREA:
0.3-6.0mm²[3248-13100]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.127[.005]
4 PLC ± -
ANGLES ± -
FINISH

MATERIAL

3

DWN
G KRUPER 1/93

CHK
R HERSEY 1/93

APVD
M ELLIS 1/93

PRODUCT SPEC
UL 486 C

APPLICATION SPEC
114-2149

WEIGHT
-

 TE Connectivity

NAME
SPLICE, WIRE, CLOSED END
22-10 AWG
-

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-36965

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
R3

1470-19 (1/15)