

Actuator

704.405.018I



<https://eao.com/p/704.405.018I>

Your product:



704.405.018I Actuator

FRONT

Front bezel material:	Aluminium
Front dimension:	Ø 35 mm
Front bezel colour:	Nature

MOUNTING

Design:	flush
Mounting cut-out:	Ø 30.5 mm

OPERATING-/INDICATION PART

Lever material:	plastic
Lever shape:	short
Lever colour:	Black

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
------------	---

MECHANICAL CHARACTERISTIC

Switching action:	Momentary - Rest - Momentary
Switching positions:	3 positions
Switching angle:	42° left / 42° right
Weight:	0.056 kg
Mechanical lifetime:	≤2.5 Mio. cycles of operation

AMBIENT CONDITION

Operating temperature:	– 40 °C ... + 55 °C
Storage temperature:	– 40 °C ... + 85 °C
IP Protection:	IP65 front side


OTHER

Short Description: Actuator, Ø 30.5 mm, Ø 35 mm, optional illuminative, Black, short, Nature, Aluminium, anodised, Momentary - Rest - Momentary


Hints: Max. 3 switching elements can be clipped on

max. number of switching elements: 3

Wiring diagrams:




Dimension drawings:



X = Screw terminal

Mounting cut-outs:



A = Screw terminal
 B = Push-in terminal (PIT)
 C = Plug-in terminal 6.3 mm x 0.8 mm
 D = Double plug-in terminal 6.3 mm x 0.8 mm

Switching positions:

