





Jan.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



NOTES 1 Rotation examples of ref No. ① and No. ⑦ are shown.
② The recommended clamp torque of ref. No. ⑩ : 0.2 to 0.3N・m.
③ Across flats of hexagon hole of ref. No. ⑩ : 1.27

5	PHOSPHOR BRONZE	NICKEL PLATING	11	CHLOROPRENE RUBBER	(BLACK)									
4	PHENOL FORMALDEHYDE	(BLACK) UL94V-0	10	STEEL	NICKEL PLATING JIS B 1177 HEXAGON SOCKET SET SCREW M2.0X0.45X2									
3	PHENOL FORMALDEHYDE	(BLACK) UL94V-0	9	BRASS	NICKEL PLATING JIS B 1111 PAN HEAD MACHINE SCREW M3X0.5X8									
2	COPPER ALLOY	SILVER PLATING 3μm min.	8	POLYACETAL										
1	ALUMINUM ALLOY	NICKEL PLATING	7	ALMINUM ALLOY	MATTE FINISH NICKEL PLATED									
			6	ALMINUM ALLOY	MATTE FINISH NICKEL PLATED									
NO.		MATERIAL		FINISH . REMARKS										
NO.		MATERIAL		FINISH . REMARKS										
UNITS mm				SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED		DATE	
 HIROSE ELECTRIC CO., LTD.		APPROVED : HY. KOBAYASHI		15. 09. 14		DRAWING NO.		EDC-119153-00-00						
		CHECKED : HY. KOBAYASHI		15. 09. 14		PART NO.		JRC16BP-7PA						
		DESIGNED : KN. IKEHARA		15. 09. 14		CODE NO.		CL114-0302-0-00						
		DRAWN : KN. IKEHARA		15. 09. 14										