


| 1 | | | 2 | | | 3 | | | 4 | | |
|-------|--------------------------|----|------|------|--|-------|--------------------------|----|------|------|--|
| COUNT | DESCRIPTION OF REVISIONS | BY | CHKD | DATE | | COUNT | DESCRIPTION OF REVISIONS | BY | CHKD | DATE | |
| △ | | | | | | △ | | | | | |
| △ | | | | | | △ | | | | | |
| △ | | | | | | △ | | | | | |
| △ | | | | | | △ | | | | | |



NOTE 1 ONE EXAMPLE OF THE ROTATION OF REF.NO.①AND NO.⑦ARE SHOWN.

② ACROSS FLATS HEXAGON HEAD OF REF.NO.⑥ : 1.27

3 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER,
PLEASE CONFIRM BEFORE THE USE.

| | | | | | |
|----------------------------|---------------------|-----------------------------|--|---|---------------------------------------|
| 5 | PHOSPHOR BRONZE | NICKEL PLATING | | | |
| 4 | PHENOL-FORMALDEHYDE | (BLACK) UL94V-0 | 9 | BRASS | NICKEL PLATING M3×0.5×10 |
| 3 | PHENOL-FORMALDEHYDE | (BLACK) UL94V-0 | 8 | ALUMINUM ALLOY | MATTE FINISH NICKEL PLATING |
| 2 | COPPER ALLOY | SILVER PLATING 3μ m min. | 7 | ALUMINUM ALLOY | MATTE FINISH NICKEL PLATING |
| 1 | ALUMINUM ALLOY | MATTE FINISH NICKEL PLATING | 6 | STEEL | NICKEL PLATING M2.6×0.45×2 |
| NO. | MATERIAL | FINISH, REMARKS | NO. | MATERIAL | FINISH, REMARKS |
| CODE NO. (OLD) CL | | | DRAWN <i>M. Sato</i> 06.12.06 | DESIGNED <i>D. Matsume</i> 06.12.18 | CHECKED <i>M. Sato</i> 06.12.19 |
| | | | APPROVED <i>M. Sato</i> 06.12.19 | | |
| | | | RELEASED | | |
| DRAWING NO. EDC4-025492 | | | PART NO. JR21JK-10S | | |
| SCALE 1 : 1 | | | CODE NO. CL114-0545-2 | | |
| UNITS mm | | | 1 1 | | |

HRS

HIROSE ELECTRIC CO., LTD.

CL114-0545-2