

**SLS 5.08/16/180 SN OR BX****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image**

Similar to illustration

Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

**General ordering data**

|              |                                                                                                                                      |
|--------------|--------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 16, 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm², Box |
| Order No.    | <a href="#">1627230000</a>                                                                                                           |
| Type         | SLS 5.08/16/180 SN OR BX                                                                                                             |
| GTIN (EAN)   | 4008190199746                                                                                                                        |
| Qty.         | 18 pc(s).                                                                                                                            |
| Product data | IEC: 400 V / 21.5 A / 0.2 - 2.5 mm²<br>UL: 300 V / 14 A / AWG 26 - AWG 12                                                            |
| Packaging    | Box                                                                                                                                  |

## SLS 5.08/16/180 SN OR BX

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 22.2 mm  | Depth (inches)  | 0.874 inch |
| Height     | 15.3 mm  | Height (inches) | 0.602 inch |
| Net weight | 27.833 g |                 |            |

## System Parameters

|                                              |                                                  |                   |                            |
|----------------------------------------------|--------------------------------------------------|-------------------|----------------------------|
| Product family                               | OMNIMATE Signal - series BL/SL 5.08              |                   |                            |
| Type of connection                           | Field connection                                 |                   |                            |
| Wire connection method                       | Clamping yoke connection                         |                   |                            |
| Pitch in mm (P)                              | 5.08 mm                                          |                   |                            |
| Pitch in inches (P)                          | 0.2 inch                                         |                   |                            |
| Conductor outlet direction                   | 180°                                             |                   |                            |
| Number of poles                              | 16                                               |                   |                            |
| L1 in mm                                     | 76.2 mm                                          |                   |                            |
| L1 in inches                                 | 3 inch                                           |                   |                            |
| Number of rows                               | 1                                                |                   |                            |
| Pin series quantity                          | 1                                                |                   |                            |
| Touch-safe protection acc. to DIN VDE 57 106 | finger-safe plugged/ back-of-hand-safe unplugged |                   |                            |
| Protection degree                            | IP20                                             |                   |                            |
| Volume resistance                            | ≤5 mΩ                                            |                   |                            |
| Can be coded                                 | Yes                                              |                   |                            |
| Stripping length                             | 7 mm                                             |                   |                            |
| Clamping screw                               | M 2.5                                            |                   |                            |
| Screwdriver blade                            | 0.6 x 3.5                                        |                   |                            |
| Screwdriver blade standard                   | DIN 5264-A                                       |                   |                            |
| Plugging cycles                              | 25                                               |                   |                            |
| Plugging force/pole, max.                    | 4 N                                              |                   |                            |
| Pulling force/pole, max.                     | 3 N                                              |                   |                            |
| Tightening torque                            | Torque type                                      | Wire connection   |                            |
|                                              | Usage information                                | Tightening torque | min. 0.4 Nm<br>max. 0.5 Nm |

## Material data

|                                       |                            |                                       |          |
|---------------------------------------|----------------------------|---------------------------------------|----------|
| Colour                                | orange                     | Colour chart (similar)                | RAL 2000 |
| Insulating material group             | IIIa                       | Comparative Tracking Index (CTI)      | ≥ 200    |
| Contact material                      | CuSn                       | Contact surface                       | tinned   |
| Layer structure of plug contact       | 4...8 µm Sn hot-dip tinned | Storage temperature, min.             | -40 °C   |
| Storage temperature, max.             | 70 °C                      | Operating temperature, min.           | -50 °C   |
| Operating temperature, max.           | 100 °C                     | Temperature range, installation, min. | -25 °C   |
| Temperature range, installation, max. | 100 °C                     |                                       |          |

## Conductors suitable for connection

|                                         |          |
|-----------------------------------------|----------|
| Clamping range, min.                    | 0.13 mm² |
| Clamping range, max.                    | 3.31 mm² |
| Wire connection cross section AWG, min. | AWG 26   |
| Wire connection cross section AWG, max. | AWG 12   |
| Solid, min. H05(07) V-U                 | 0.2 mm²  |
| Solid, max. H05(07) V-U                 | 2.5 mm²  |
| Flexible, min. H05(07) V-K              | 0.2 mm²  |
| Flexible, max. H05(07) V-K              | 2.5 mm²  |

Creation date September 16, 2022 8:29:06 AM CEST

## SLS 5.08/16/180 SN OR BX

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm<sup>2</sup> min.w. plastic collar ferrule, DIN 46228 pt 4, 2.5 mm<sup>2</sup> max.w. wire end ferrule, DIN 46228 pt 1, 0.2 mm<sup>2</sup> min.w. wire end ferrule, DIN 46228 pt 1, 2.5 mm<sup>2</sup> max.

Plug gauge in accordance with EN 60999 a x b; ø 2.8 mm x 2.0 mm; 2.4 mm

|                     |                                        |                              |                         |      |
|---------------------|----------------------------------------|------------------------------|-------------------------|------|
| Clampable conductor | Cross-section for conductor connection | Type                         | fine-wired              |      |
|                     |                                        | nominal                      | 0.5 mm <sup>2</sup>     |      |
|                     | wire end ferrule                       | Stripping length             | nominal                 | 6 mm |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H0.5/6</a>  |      |
|                     | Cross-section for conductor connection | Type                         | fine-wired              |      |
|                     |                                        | nominal                      | 1 mm <sup>2</sup>       |      |
|                     | wire end ferrule                       | Stripping length             | nominal                 | 6 mm |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H1.0/6</a>  |      |
|                     | Cross-section for conductor connection | Type                         | fine-wired              |      |
|                     |                                        | nominal                      | 1.5 mm <sup>2</sup>     |      |
|                     | wire end ferrule                       | Stripping length             | nominal                 | 7 mm |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H1.5/7</a>  |      |
|                     | Cross-section for conductor connection | Type                         | fine-wired              |      |
|                     |                                        | nominal                      | 2.5 mm <sup>2</sup>     |      |
|                     | wire end ferrule                       | Stripping length             | nominal                 | 7 mm |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H2.5/7</a>  |      |
|                     | Cross-section for conductor connection | Type                         | fine-wired              |      |
|                     |                                        | nominal                      | 0.75 mm <sup>2</sup>    |      |
|                     | wire end ferrule                       | Stripping length             | nominal                 | 6 mm |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H0.75/6</a> |      |

Reference text The outside diameter of the plastic collar should not be larger than the pitch (P), Length of ferrules is to be chosen depending on the product and the rated voltage.

## Rated data acc. to IEC

|                                                                           |                        |                                                                       |                   |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|-------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 21.5 A            |
| Rated current, max. number of poles (Tu=20°C)                             | 16 A                   | Rated current, min. number of poles (Tu=40°C)                         | 18 A              |
| Rated current, max. number of poles (Tu=40°C)                             | 14 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 400 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 320 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 250 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV                   | Short-time withstand current resistance                               | 3 x 1s with 120 A |

## SLS 5.08/16/180 SN OR BX

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

## Technical data

## Rated data acc. to CSA

Institute (CSA)



Certificate No. (CSA)

www.weidmueller.com

200039-1121690

|                                   |                                                                        |
|-----------------------------------|------------------------------------------------------------------------|
| Rated voltage (Use group B / CSA) | 300 V                                                                  |
| Rated current (Use group B / CSA) | 15 A                                                                   |
| Wire cross-section, AWG, min.     | AWG 26                                                                 |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate. |

|                                   |        |
|-----------------------------------|--------|
| Rated voltage (Use group D / CSA) | 300 V  |
| Rated current (Use group D / CSA) | 10 A   |
| Wire cross-section, AWG, max.     | AWG 12 |

## Packing

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 338 mm |
| VPE width | 130 mm | VPE height | 27 mm  |

## Type tests

|                                                           |                |                                               |           |
|-----------------------------------------------------------|----------------|-----------------------------------------------|-----------|
| Test: Durability of markings                              | Standard       | VDE 0627 Tab. 7 item 3/6.86                   |           |
|                                                           | Test           | durability                                    |           |
|                                                           | Evaluation     | passed                                        |           |
| Test: Clampable cross section                             | Standard       | VDE 0609 part 1 06.83, EN 60947-1 03.91       |           |
|                                                           | Conductor type | Type of conductor and conductor cross-section | H05V-U0.5 |
|                                                           |                | Type of conductor and conductor cross-section | H05V-K0.5 |
|                                                           |                | Type of conductor and conductor cross-section | H05V-U2.5 |
|                                                           |                | Type of conductor and conductor cross-section | H05V-K2.5 |
|                                                           |                | Type of conductor and conductor cross-section | AWG 28    |
|                                                           |                | Type of conductor and conductor cross-section | AWG 14    |
|                                                           | Evaluation     | passed                                        |           |
| Test for damage to and accidental loosening of conductors | Standard       | EN 60947-1/1991 section 8.2.4.3               |           |
|                                                           | Requirement    | 0.3 kg                                        |           |
|                                                           | Conductor type | Type of conductor and conductor cross-section | H05V-U0.5 |
|                                                           |                | Type of conductor and conductor cross-section | H05V-K0.5 |
|                                                           | Evaluation     | passed                                        |           |
|                                                           | Requirement    | 0.7 kg                                        |           |
|                                                           | Conductor type | Type of conductor and conductor cross-section | H07V-U2.5 |
|                                                           |                | Type of conductor and conductor cross-section | H07V-K2.5 |
|                                                           | Evaluation     | passed                                        |           |

## SLS 5.08/16/180 SN OR BX

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

EN 60947-1/1991 section 8.2.4.4

≥5 N info@weidmueller.com

Type of conductor and conductor cross-section AWG 28/1

Type of conductor and conductor cross-section AWG 28/7

passed

≥50 N

Type of conductor and conductor cross-section H07V-U2.5

Type of conductor and conductor cross-section H07V-K2.5

Type of conductor and conductor cross-section AWG 14/19

passed

## Technical data

## Pull-out test

Standard

Requirement

Conductor type

Evaluation

Requirement

Conductor type

Evaluation

## Classifications

ETIM 6.0

EC002638

ETIM 7.0

EC002638

ETIM 8.0

EC002638

ECLASS 9.0

27-44-03-09

ECLASS 9.1

27-44-03-09

ECLASS 10.0

27-44-03-09

ECLASS 11.0

27-46-02-02

ECLASS 12.0

27-46-02-02

## Important note

## IPC conformity

Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

## Notes

- Additional variants on request
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- Long term storage of the product with average temperature of 50 °C and average humidity 70%, 36 months

## Approvals

## Approvals



ROHS

Conform

UL File Number Search

UL Website

Certificate No. (UR)

E60693

## SLS 5.08/16/180 SN OR BX

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|---------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of the Manufacturer</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Brochures                                   | <a href="#">FL DRIVES EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">FL BUILDING SAFETY EN</a><br><a href="#">FL APPL LED LIGHTING EN</a><br><a href="#">FL INDUSTR.CONTROLS EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL_BASE_STATION_EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">PO OMNIMATE EN</a> |

## SLS 5.08/16/180 SN OR BX

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0


Fax. +49 5231 14-2083

## Drawings


**Dimensional drawing** [info@weidmueller.com](mailto:info@weidmueller.com)




## Graph



## Graph



## Graph



WEIDMÜLLER INTERFAC GmbH & Co.KG

WEITERGABE SOWIE Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksunterzeichnung vorbehalten. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED. OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. WEIDMÜLLER EXCLUSIVELY RESERVES THE RIGHT TO FILE FOR PATENTS, UTILITY MODELS OR DESIGNS.

MASS E OHNE TOLERANZ SIND KEINE PRUEFMASSE  
DIMS. WITHOUT TOLERANCE ARE NOT CONTROL DIMS.


ALLGEMEINGUELTIGE KUNDENZEICHNUNG, AKTUELLER STAND NUR AUF ANFRAGE  
GENERAL CUSTOMER DRAWING, TOPICAL VERSION ONLY IF REQUIRED

DIE DEUTSCHE VERSION IST VERBINDLICH  
THE GERMAN VERSION IS BINDING


SHOWN: SLS 5.08/04/180



SCREWDRIVER



CONDUCTOR




SHOWN: SLS 5.08/04/180B



SCREWDRIVER






CONDUCTOR



For the mounting of PCBs, it should be noted that the rated data relates only to the PCB components alone.  
The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 664 / VDE 0110.  
The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.


Weidmüller PCB components are tested to the DIN EN 61984 standard, and are valid for its field of application. Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

SHOWN: SLS 5.08/04/180DF



|                                  |                                    |        |          |
|----------------------------------|------------------------------------|--------|----------|
| 0.5-0.8                          | 0.019-0.031                        | 6.3    | 0.248    |
| 1.00                             | 0.039                              | 6.4    | 0.252    |
| 1.5                              | 0.059                              | 6.5    | 0.256    |
| 2.00                             | 0.079                              | 6.7    | 0.264    |
| WANDDICKE<br>WALL THICKNESS [mm] | WANDDICKE<br>WALL THICKNESS [inch] | d [mm] | d [inch] |

SCREWDRIVER



|    |                  |                      |
|----|------------------|----------------------|
| 24 | 106.84           | 4.600                |
| 23 | 111.76           | 4.400                |
| 22 | 106.68           | 4.200                |
| 21 | 101.60           | 4.000                |
| 20 | 96.52            | 3.800                |
| 19 | 91.44            | 3.600                |
| 18 | 86.36            | 3.400                |
| 17 | 81.28            | 3.200                |
| 16 | 76.20            | 3.000                |
| 15 | 71.12            | 2.800                |
| 14 | 66.04            | 2.600                |
| 13 | 60.96            | 2.400                |
| 12 | 55.88            | 2.200                |
| 11 | 50.80            | 2.000                |
| 10 | 45.72            | 1.800                |
| 9  | 40.64            | 1.600                |
| 8  | 35.56            | 1.400                |
| 7  | 30.48            | 1.200                |
| 6  | 25.40            | 1.000                |
| 5  | 20.32            | 0.800                |
| 4  | 15.24            | 0.600                |
| 3  | 10.16            | 0.400                |
| 2  | 5.08             | 0.200                |
| n  | POLZAHL<br>POLES | L1 [mm]<br>L1 [inch] |

P=5.08 RASTER PITCH

METRIC TOLERANCES  
X. = ±0.3  
X.X = ±0.1  
X.XX = ±0.05

70327/5  
22.05.13 HELIS\_MA

01

MODIFICATION

DRAWN  
27.08.2003

RESPONSIBLE

CHECKED  
27.05.2013

APPROVED

DATE  
27.08.2003

NAME  
#AttributeError: Benutzer None nicht gefunden.  
HERTEL\_S  
HECKERT\_M  
HECKERT\_M

**SLS 5.08/.. /180...**  
STIFTSTECKER  
MALE PLUG

CAT.NO.:  
**C 21277**  
DRAWING NO.  
SHEET 01

18  
ISSUE NO.  
OF 01 SHEETS

PRODUCT FILE: SLS 5.08

7314