






LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	C3	REVISED PER ECR-13-015346		03OCT2013	KH	GJ	

- SPECIFICATIONS:
MAGNET WIRE #18 - #34 AWG,
.040"(1.02mm)-.006"(0.16mm) DIA COPPER.
OTHER SIZES MAY BE ACCOMMODATED,
CONSULT TYCO ELECTRONICS FOR APPROVAL.
- POCKET RECOMMENDATION:
#1601424
- TERMINAL APPLICATION TO COMPLY WITH
TYCO ELECTRONICS SPECIFICATION 114-13166.
CONSULT TYCO ELECTRONICS ENGINEERING
FOR THE PROPER INSERTION DEPTH.
- TIP MAY BE RADIUSED WITHIN DIMENSIONS
SHOWN AND HAVE CONVEX SIDES.
- TWO(2) TERMINALS SHOWN FOR ILLUSTRATION
PURPOSES ONLY
- PRELIMINARY - NOT FOR PRODUCTION



-		-	-
-		-	-
-		-	-
PRE-TIN PLATE OVER NICKEL UNDERPLATE		-	2-1601042-3
SELECTIVE POST TIN PLATE OVER NICKEL UNDERPLATE		131-090-120	2-1601042-2
UNPLATED		131-089-000	1601042-1
FINISH		REFERENCE PART NUMBER	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.WELLER CHK M.FEHER APVD K.RANDOLPH PRODUCT SPEC 108-2085 APPLICATION SPEC	NAME
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .01[0.25] 3 PLC ± .005[0.13] 4 PLC ± - ANGLES ± 2°	SIZE A2
MATERIAL BRASS, 3/4 HARD		FINISH SEE TABLE	CAGE CODE 00779
		WEIGHT -	DRAWING NO C=1601042
		CUSTOMER DRAWING	RESTRICTED TO -
		SCALE 1:1	SHEET 1 of 1
			REV C3