

## SUMMARY

### # Wires

Low voltage 4



*Image is for illustrative purpose only*

|                  |                                   |
|------------------|-----------------------------------|
| Series           | OK                                |
| Termination type | Female solder                     |
| IP rating        | 68                                |
| AWG wire size    | 30.00 - 22.00                     |
| Cable Ø          | 3.60 - 4.00 mm                    |
| Status           | active                            |
| Matching parts   | <a href="#">FGG.0K.304.CLAC40</a> |

### Download

[Request a quote](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

|                   |                                                                                                                               |
|-------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Shell Style/Model | PH*: Free receptacle, cable collet and nut for fitting a bend relief                                                          |
| Keying            | 1 key (alpha=0, plug: male contacts, receptacle: female contacts)                                                             |
| Housing Material  | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Variant           | Z : Nut for fitting a bend relief                                                                                             |
| Weight            | 14.58 g                                                                                                                       |

### Performance

|               |                           |
|---------------|---------------------------|
| Configuration | OK.304 : 4 Low Voltage    |
| Insulator     | L: PEEK (UL 94 / V-0/1.5) |
| Rated Current | 7 Amps                    |

### Specifications

Contact Type: Solder  
Contact Dia.: 0.7 mm (0.028in)  
Bucket Dia.: 0.8 mm (0.031in)  
Max. Solid Conductor: 0.34 mm<sup>2</sup> (AWG 22)  
Max. Stranded Conductor: 0.34 mm<sup>2</sup> (AWG 22)  
R (max): 6.1 mOhm


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Vtest (contact-shell): 700 V (AC), 990 V (DC)  
Vtest (contact-contact): 850 V (AC), 1200 V (DC)

Others

Endurance (Shell): 5000 mating cycles  
Temp (min / max): -55°C / +200°C  
Humidity (max): <=95% [at 60 deg C / 140 F]  
Vibration: 15 g [10 Hz - 2000 Hz]  
Shock Resistance: 100 g [ 6 ms]  
Climatical Category: 50/175/21  
Shielding (min): 95 dB (10 MHz)  
Shielding (min): 80 dB (1 GHz)  
Salt Spray Corrosion: >1000 hr

DRAWINGS



Dimensions

|     | A    | L    | S2   |
|-----|------|------|------|
| mm. | 13   | 34   | 7    |
| in. | 0,51 | 1,34 | 0,28 |

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Spanner wrench: [DCD.OE.007.PA070](#)

Cables

|       |      |       |                                                                                     |
|-------|------|-------|-------------------------------------------------------------------------------------|
| 40080 | PVC  | Black |                                                                                     |
| 40086 | PVC  | Blue  |                                                                                     |
| 40140 | PVC  | Black |  |
| 40240 | PTFE | White |  |

*LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*