

Actuator

704.032.2



<https://eao.com/p/704.032.2>

Your product:



704.032.2
Actuator

FRONT

Front bezel colour:	Nature
Front dimension:	Ø 29 mm
Front form:	round
Front bezel material:	Aluminium

MOUNTING

Design:	raised
---------	--------

OPERATING-/INDICATION PART

Lens colour:	Red
Lens shape:	flush
Lens material:	Plastic
Lens illumination:	illuminative
Lens optics:	transparent

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
------------	---

MECHANICAL CHARACTERISTIC

Operating Travel:	ca. 5.8 mm ± 0.2 mm
Terminal:	Screw terminal
Mechanical lifetime:	≤3 Mio. cycles of operation


Operating force:	8 N
Switching action:	Momentary
Weight:	0.056 kg

AMBIENT CONDITION


IP Protection:	IP65 front side
Operating temperature:	– 40 °C ... + 55 °C
Storage temperature:	– 40 °C ... + 85 °C

OTHER


max. number of switching elements:	3
Hints:	Frontring with protective cover to be mounted with a torque of 0.4 Nm onto actuator, Max. 3 switching elements can be clipped on
Housing material:	Plastic
Short Description:	Actuator, Ø 29 mm, flush, illuminative, Red, Plastic, transparent, round, Nature, Aluminium, anodised, Momentary, Screw terminal
Housing colour:	Grey



Wiring diagrams:



Mounting cut-outs:



A = Screw terminal

B = Push-in terminal (PIT)

C = Plug-in terminal 6.3 mm x 0.8 mm

D = Double plug-in terminal 6.3 mm x 0.8 mm