





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	20OCT2020	AJ	SH
	A1	REVISED PER ECR-20-015843	06NOV2020	IT	SH





2366031-1 AS SHOWN
SCALE 3:1




- 1 MATERIAL:
CAGE ASSEMBLY - 0.25mm THICK STAINLESS STEEL.
EMI SPRINGS - COPPER ALLOY.
HEAT SINK - ALUMINUM
CLIP - STAINLESS STEEL.
LIGHT PIPE - CLEAR POLYCARBONATE
- 2 FINISH
EMI SPRINGS - NICKEL PLATING, NON-PLATED EDGES PERMISSIBLE.
HEAT SINK - SEE TABLE
3. MATES WITH SFP-DD MSA COMPLIANT TRANSCEIVERS.
- 4 DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
5. MINIMUM PC BOARD THICKNESS:
SINGLE SIDED = 1.57 mm
DOUBLE SIDED = 2.20 mm
- 6 REFERENCE APPLICATION SPEC. 114-60027, HOLE A, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- 7 REFERENCE APPLICATION SPEC. 114-60027, HOLE B, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
8. DATUM -A- IS TOP SURFACE OF THE HOST BOARD.
- 9 MAXIMUM HEIGHT WITH MODULE INSERTED.



2366031-1 AS SHOWN
SCALE 4:1




DETAIL A
SCALE 16:1




NICKEL PLATING	WITHOUT	SEE SHEET 2	2366031-3
NICKEL PLATING	WITH	SEE SHEET 2	2366031-2
BLACK ANODIZE	WITH	SEE SHEET 1	2366031-1
HSK FINISH	LIGHT PIPE	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ARTHUR JIN 22NOV2019	 TE Connectivity				
		CHK SEAN HAN 22NOV2019					
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CAGE ASSEMBLY, SFPDD 1X1 W/ GENERAL HS -	SIZE A1	CODE 00779	DRAWING NO G-2366031	RESTRICTED TO -
mm	0 PLC ±.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.10 4 PLC ±. ANGLES ±.						
			PRODUCT SPEC 108-60128				
			APPLICATION SPEC 114-60027				
MATERIAL	FINISH	WEIGHT	CUSTOMER DRAWING				
-	-	-	SCALE 2:1 SHEET 1 OF 5 REV. A1				


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




2366031-2 AS SHOWN
SAME AS -1 EXCEPT DIFFERENT HEAT SINK
SCALE 4:1



2366031-2 3D VIEW
SCALE 3:1








2366031-3 AS SHOWN
SAME AS -2 EXCEPT WITHOUT LIGHT PIPE
SCALE 4:1




2366031-3 3D VIEW
SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: ARTHUR JIN 22NOV2019	TE Connectivity	
		CHK: SEAN HAN 22NOV2019		
DIMENSIONS:		APVD: -	NAME: CAGE ASSEMBLY, SFPDD 1X1 W/ GENERAL HS	
mm		PRODUCT SPEC: 108-60128	SIZE: A1	
		APPLICATION SPEC: 114-60027	CAGE CODE: 00779	
		WEIGHT: -	DRAWING NO: C=2366031	
MATERIAL: -		CUSTOMER DRAWING		RESTRICTED TO: -
		SCALE: 2:1		SHEET: 2 OF 5
				REV: A1



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: ARTHUR JIN 22NOV2019	TE Connectivity		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK: SEAN HAN 22NOV2019			
DIMENSIONS:		APVD: -	NAME: CAGE ASSEMBLY, SFPDD 1X1 W/ GENERAL HS		
mm		PRODUCT SPEC: 108-60128	SIZE: A1 CAGE CODE: 00779 DRAWING NO: 2366031		
		APPLICATION SPEC: 114-60027			
MATERIAL: -		WEIGHT: -	RESTRICTED TO: -		
-		CUSTOMER DRAWING			
			SCALE: 2:1	SHEET: 3 OF 5	REV: A1



REVISIONS				
P	LTR	DESCRIPTION	DATE	OWN APVD
		SEE SHEET 1		



DETAIL D
SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: ARTHUR JIN 22NOV2019	NAME: CAGE ASSEMBLY, SFPDD 1X1 W/ GENERAL HS	
DIMENSIONS:		CHK: SEAN HAN 22NOV2019		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD: -	PRODUCT SPEC: 108-60128	RESTRICTED TO: -
	0 PLC ±0.25		APPLICATION SPEC: 114-60027	
	1 PLC ±0.20		SIZE: A1	
	2 PLC ±0.10		CAGE CODE: 2366031	
	3 PLC ±0.10		DRAWING NO: 100779	
	4 PLC ±0.10		SCALE: 2:1	
MATERIAL: -	FINISH: -	WEIGHT: -	SHEET: 5 OF 5	
CUSTOMER DRAWING		REV: A1		