




**Pushing Performance**  
Since 1945

# Han-Yellock 60 carrier hood push button



Part number	11 12 600 0114
Specification	Han-Yellock 60 carrier hood push button

## Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Carrier hood
Description of hood/housing	Push button, slot

## Version

Size	Han-Yellock® 60
Locking type	Push button
Field of application	Hoods/housings for industrial applications

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Un-/locking temperature	-10 ... +85 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

## Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Passivated
Colour (hood/housing)	Metallic
Material (seal)	NBR



**Pushing Performance**  
Since 1945

## Material properties

Material (locking)	Polyamide (PA) Stainless steel
Colour (locking)	Melon yellow
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel Naphthalene

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	248 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140110182
ETIM	EC000437
eCI@ss	27440202 Shell for industrial connectors