


# Actuator

704.409.0



<https://eao.com/p/704.409.0>

Your product:

---



## 704.409.0 Actuator

### FRONT

<b>Front dimension:</b>	Ø 29 mm
<b>Front bezel material:</b>	Aluminium
<b>Front bezel colour:</b>	Nature

### MOUNTING

<b>Design:</b>	raised
----------------	--------

### OPERATING-/INDICATION PART

<b>Lever shape:</b>	short
<b>Lever material:</b>	plastic
<b>Lever colour:</b>	Black

### ELECTRICAL CHARACTERISTICS

<b>Standards:</b>	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
-------------------	---

### MECHANICAL CHARACTERISTIC

<b>Weight:</b>	0.034 kg
<b>Switching positions:</b>	3 positions
<b>Switching action:</b>	Momentary - Rest - Maintained
<b>Mechanical lifetime:</b>	≤2.5 Mio. cycles of operation
<b>Switching angle:</b>	42° left / 42° right

## AMBIENT CONDITION

**Operating temperature:** - 40 °C ... + 55 °C

**Storage temperature:** - 40 °C ... + 85 °C

**IP Protection:** IP65 front side


## OTHER

**max. number of switching elements:** 3

**Short Description:** Actuator, Ø 29 mm, non illuminative, Black, short, Nature, Aluminium, anodised, Momentary - Rest - Maintained


**Hints:** Max. 3 switching elements can be clipped on

**Dimension drawings:**



A = Screw terminal

**Mounting cut-outs:**



A = Screw terminal

B = Push-in terminal (PIT)

C = Plug-in terminal 6.3 mm x 0.8 mm

D = Double plug-in terminal 6.3 mm x 0.8 mm

**Wiring diagrams:**



**Switching positions:**

