


Für diese Unterlage behalten wir uns alle Rechte vor, auch für den Fall der Patenterteilung oder Gebrauchsmustereintragung. Sie darf ohne unsere vorherige schriftliche Zustimmung weder vervielfältigt noch sonstwie benutzt, noch Drillen zugänglich gemacht werden.

Nur rol gestempelte oder auf Laufkarte gedruckte Dokumente unterliegen dem Änderungsdienst und sind zur Fertigung freigegeben. Only red stamped or on jobcard printed documents are managed. These documents are approved for production.


All Rights reserved, including possible patents or trademarks. Documents shall not be provided to a third party or duplicated in any form without prior written permission.

CAD: Pro/ENGINEER



Additional coding
View in direction B




K10YBR-P09WCD0-0000
Mechanical coding: B
Color coding: red



K10YAR-P09WCD0-0000
Mechanical coding: A
Color coding: light brown




K10YCR-P09WCD0-0000
Mechanical coding: C
Color coding: blue



Delivery condition
2:1

Only insert
View in direction A
8:1



Technical information

- Max. cable Ø5.5mm (Based on cable with one braided shield)
- Solder contacts: AWG26
- Current load: 5A@Δ+40° (Single contact)
3.25A@Δ+40° (Insert)
- Test voltage: 600V (acc. SAE AS 13441:1998, Contact to contact)
- Rated voltage: 200V (acc. SAE AS 13441:1998) 2)

- For more technical information and accessories see catalogue (www.odu.de/amc)

1) For crimp information, torque, etc. see assembly instruction 010.645.001.000.003 (www.odu.de/amc/assembly)

2) Maximal operating voltage at sea level up to 2.000m. Rated voltage applies no other electrical safety standard. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. This must be evaluated in the frame of equipment engineering.

All shown connectors are according to DIN EN 61984:2009
connectors without breaking capacity (COC) !

				Dimensions without tolerances acc. to middle DIN ISO 2768			PE-modell-nr.:	
						CAD-nr.:		sheet.:
				2011	date	name	designation: In-Line Receptacle AMC Standard Version	scale:
				prep.	13.09.	M. Meier		4 : 1
				app.				
				norm.				
				 otto dunkel gmbh			drawing nr.:	copy
							K10Y.R-P09WCD0-0000	nr.
index	notice	date	name				replacement for:	