






LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00				
	A	RELEASED	17MAR06	BM	SS
	A1	REVISED PER ECO-06-018770	04AUG06	BM	SS
	A2	REVISED PER ECO-06-029973	28DEC2006	CJV	SAS


- 1
- 2
- 3
- 4
- 5
- 6
- INSERT: LCP, UL 94V-0 RATED.
CONTACTS: COPPER ALLOY
SHELL: PHOSPHOR BRONZE.
- CONTACTS: 1.27µm MINIMUM GOLD OVER
3.81µm MINIMUM NICKEL ON MATING END.
3.81µm MINIMUM MATTE TIN OVER
1.27µm MINIMUM NICKEL ON SOLDER TAILS.
SHELL: 3µm MINIMUM TIN OVER
1.27µm MINIMUM NICKEL.
- DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
- LOCATION OF STANDOFF CONTACTING THE BOARD.
- PACKAGED TAPE AND REEL
- TYCO LOGO, COUNTRY OF ORIGIN, MATERIAL CODE, BUILDING NUMBER AND MOLD CAVITY ID ARE FROSTED ON THIS SURFACE.




RECOMMENDED
SOLDER STENCIL
LAYOUT
SCALE 5:1



DETAIL J
SCALE 8:1



5	SOLDER TAIL WITH BOARDLOCK	1888372-1
PACKAGING	DESCRIPTION	PART NUMBER
DWN B MCMMASTER 17MAR06 CHK S SHUEY 17MAR06 APVD S SHUEY 17MAR06	NAME RECEPTACLE ASSEMBLY, FIBRE CHANNEL, SURFACE MOUNT, SINGLE ROW, HSSDC2	
PRODUCT SPEC 108-1965 APPLICATION SPEC 114-13028 WEIGHT 2.71	SIZE A2 CAGE CODE 00779 DRAWING NO C-1888372	RESTRICTED TO -
CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 3 REV A2





RECOM

0.05±0.10
TOP OF PCB TO
PANEL OPENING

DETAIL K
SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN B. MCMASTER 17MAR06 CHR S. SHUEY 17MAR06 APVD S. SHUEY 17MAR06		tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±3° FINISH		NAME RECEPTACLE ASSEMBLY, FIBRE CHANNEL, SURFACE MOUNT, SINGLE ROW, HSSDC2	
MATERIAL		PRODUCT SPEC 108-1965 APPLICATION SPEC 114-13028 WEIGHT 2.71		SIZE A2 CAGE CODE 00779 DRAWING NO C-1888372	
CUSTOMER DRAWING		SCALE 3:1		SHEET 2 OF 3 REV A2	



—CONNECTOR MATING END
THIS SIDE

TAPE AND REEL
PACKAGING ORIENTATION 
SCALE: NTS

PIN ASSIGNMENTS
REFERENCE ONLY
SCALE: NTS

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION		DWN B. MCMASTER CHK S. SHUEY APVD S. SHUEY	17MAR06 17MAR06 17MAR06	tyco Electronics	Tyco Electronics Harrisburg, PA 17105-3608
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±3° FINISH	PRODUCT SPEC 108-1965 APPLICATION SPEC 114-13028	NAME RECEPTACLE ASSEMBLY, FIBRE CHANNEL, SURFACE MOUNT, SINGLE ROW, HSSDC2		
		WEIGHT 2.71	SIZE A2	CAGE CODE 00779	DRAWING NO C-1888372
MATERIAL		CUSTOMER DRAWING	SCALE 3.1	SHEET 3 OF 3	REV A2