

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		A	NEW RELEASE PER ECO-16-000996	140221	SG	JPF

Technical drawing of a CFX26x1108xxx connector assembly. The drawing shows a cross-section of the assembly with various components labeled. Key dimensions include a total length of 3.376 REF. and a diameter of Ø .984 MAX. The assembly consists of a BLUE COLOR BAND REF., a SHELL, PLUG R.F.I. ASSEMBLY, and an ENVIRONMENTAL BACKSHELL. The part number CFX26x1108xxx is printed on the side of the assembly.

CFX26 (x) 1 1108 (x) 2 Z (x) 3 xxx

MODIFICATION

KEYING POSITION:  
N, A, B, C, D, E

CONTACT TERMINATION:  
Z = CRIMPED CONTACT  
A THROUGH Y = EXTENDED CONTACT

CONTACT FINISH:  
P = PIN LOCALIZED GOLD FINISH  
S = SOCKET LOCALIZED GOLD FINISH  
F = PIN FULL GOLD FINISH  
G = SOCKET FULL GOLD FINISH  
H = PIN HI REL FINISH  
J = SOCKET HI REL FINISH  
A = LESS PIN CONTACT  
B = LESS SOCKET CONTACT

SHELL SIZE/INSERT ARRANGMENT




PLATING/SHELL MATERIAL:  
SEE TABLE

BASIC IDENTIFIER

4.			3
PART NUMBER (x) 1	PLATING	SHELL MATERIAL	
M	NICKEL	COMPOSITE	
J	O.D. CAD	COMPOSITE	
F	NICKEL	ALUMINUM	
W	O.D. CAD	ALUMINUM	
S	NICKEL	STAINLESS STEEL	2
T	TEFLON NICKEL	ALUMINUM	2
Z	BLACK ZINC NICKEL	ALUMINUM	2

SIZE 11 PART NUMBER (x) <sub>3</sub>	POS
CFX26x1108xZN	N
CFX26x1108xZA	A
CFX26x1108xZB	B
CFX26x1108xZC	C
CFX26x1108xZD	D
CFX26x1108xZE	E

6. COMPOSITE WEIGHT WITHOUT MODULES AND CABLE: 0.050 POUNDS.  
METAL WEIGHT WITHOUT MODULES AND CABLE: 0.078 POUNDS.  
PIN MODULE WEIGHT: .005 LBS.  
SOCKET MODULE WEIGHT: .011 LBS.
5. MATES WITH CFX20x1108xxx OR CFX24x1108xxx.
4. FINISH: SHELL/BACKSHELL - SEE TABLE.  
CONTACTS - SEE PART NUMBER BREAKDOWN.
3. MATERIAL: SHELL & COUPLING RING - SEE TABLE.  
BACKSHELL BODY/COUPLING RING - ALUMINUM ALLOY.  
CONTACTS - COPPER ALLOY.  
RESILIENT INSERTS/BACKSHELL GROMMET - SILICONE ELASTOMER.  
PLASTIC INSERTS - THERMOPLASTIC.
2. FOR AVAILABILITY CONSULT FACTORY.
1. ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JPF	140219	 TE Connectivity			
		CHK JPF	160122	NAME CONNECTOR, PLUG THREADED COUPLING 1108 ARRANGEMENT			
DIMENSIONS: INCHES		APVD AR	160122				
		PRODUCT SPEC		SIZECAGE CODEDRAWING NORESTRICTED TO			
		-					
TOLERANCES UNLESS OTHERWISE SPECIFIED:  0 PLC ±1 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.005 4 PLC ±0.0005 ANGLES ±0.5		APPLICATION SPEC		A211139C-CFX26x1108xxx-			
		-					
MATERIAL		WEIGHT		-			
		CUSTOMER DRAWING		SCALE3.000SHEET1OF1REV A			
