

Actuator

71-658.0



<https://eao.com/p/71-658.0>

Your product:



71-658.0 Actuator

OPERATING-/INDICATION PART

Lever material: plastic

Lever shape: short

ELECTRICAL CHARACTERISTICS

Surge voltage resistance: 2500 VAC, 50 Hz, 1 minute, as per DIN / IEC 60512-2 between all terminals and earth

Recommended minimum operational data:

Voltage	5 VAC/DC
Current	10 mA

Switching voltage and switching current:

Switch rating AC $\cos\phi$ 0,7 ... 0,8
gemäß EN IEC 60947-5-1

Voltage	250 VAC
Current	3 A

Switch rating DC
gemäß EN IEC 60947-5-1

Voltage	24 VDC	250 VDC
Current	3 A	0.5 A

MECHANICAL CHARACTERISTIC

Weight: 0.003 kg

Switching angle: 90° left / 42° right

Switching action: Maintained - Rest - Momentary

Switching positions: 3 positions

Mechanical lifetime: 100 000 cycles of operation

Switching system: Self-cleaning, double-break snap action switching system, 1 normally closed and 1 normally open contact per element.

Tightening torque: Fixing nut max. 0.5 Nm

AMBIENT CONDITION


Operating temperature:	– 25 °C ... + 55 °C
Storage temperature:	– 40 °C ... + 85 °C
Climate resistance:	Damp heat, steady: 56 days, + 40 °C/93 % relative humidity, according to EN IEC 60068-2-78
IP Protection:	IP65 front side
Vibration resistance:	Max. 100 m / s ² from 10 Hz ... 500 Hz, (sinusoidal EN IEC 60068-2-6)
Shock resistance:	Max. 500 m/s ² , pulse width, 3-axis (sinusoidal EN IEC 60068-2-27)

CERTIFICATE


Conformities:	CE, UKCA, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)
----------------------	---

OTHER



Housing material:	Plastic, according to UL 94 V0
Hints:	Pitch of the front plate mounting holes must agree with the printed circuit board holes Ø 3.5 mm
Short Description:	Actuator, optional illuminative, short, Maintained - Rest - Momentary
Switching positions:	



Wiring diagrams:



Mounting cut-outs:



Dimension drawings:

