








Notes:

1. Electrical Specifications:

- Meets USB 2.0 Specification
- Contact Resistance: 30 mOhm max.
- Insulation Resistance: 1000 MOhm min. @ 100 VDC
- Current Rating: 1.5 A max. at 25° C
- Working Voltage: 30 V (RMS) max.
- DWV: 500 VAC/60s at sea level
- Operating Temperature: -40° C to +85° C

2. Material and Finish:

- Receptacle Housing and Protective Cover: Polyester, UL94 V-0, Color: Black
- Panel Nut: Brass, Finish: Nickel Plated
- Panel and Cover Gasket: Silicon, Color: White
- Tether: Polycarbonate, Color: Black
- USB Adaptor Insulator: PBT, UL94 V-0, Black
- USB Adaptor Metal Shell: Copper Alloy, Nickel Plated
- USB Adaptor Overmold material: PBT UL94 V-0, Color: Black
- USB Contacts: Copper Alloy, Finish: 30 u" Gold min. over Nickel

3. Connector can be mounted to a maximum panel thickness of 3.2 mm.

4. IP67 rated when covered or fully mated with the appropriated mating connector

Directive 2002/95/EC RoHS Compliant

Version	Part Number
Plastic Version	17-210141
Metallized Plastic Version	17-210181

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. CONEC CORPORATION OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION	DO NOT ALTER CAD DRAWING BY HAND	Customer:			Tolerance Unless otherwise specified			Scale:		Dim. in mm		
		Name		Title	Approval Date	0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3°		Autodesk Inventor		Material: See Notes		
						2012	Date	Name		Receptacle + Cover Assembly Kit Both Sides Bayonet Receptacle Housing with USB Type A F/F Adaptor		
						Draw.	Sept. 28	Vincent Ke				
						Appd.	Sept. 28	J. Chaudry				
						Norm						
		c	3 x c	Jan/18/2013	Vincent Ke	D-old				Drawing No.: 17K1A357		DIN A3
		b	1 x b	Oct/17/2012	Vincent ke					Part No.: SEE PART NUMBER TABLE		Sheet 1/1
		a	original									
		Rev.	Changes	Date	Name							

CONEC

DIN
A3
Sheet
1/1