






RECOMMENDED PANEL CUTOUT
MAX. PANEL THICKNESS 1-6mm



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- RATING: 2A 36 VDC
- ELECTRIC LIFE: 200,000 CYCLES
- DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
- CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
- OPERATING TEMP.: -20°C to 70°C
- ▲ DENOTES CRITICAL PARAMETER.
- LAMP VOLTAGE: 20mA 3.1V TYP.
- TRAVEL: 1.80mm
- ACTUATION FORCE: 4.5 $\pm$ 1.5 N
- MOUNTING NUT TORQUE: 1-3 Nm
- INGRESS PROTECTION: IP67, IK10
- HARDWARE SUPPLIED: O-RING AND HEXNUT



REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®				OBJECT ID
B	ECO-101693	print update	03/06/23	MW	TITLE SV7F23SS-301				100121961
					SCALE 1:1	DATE 5/10/2022	DR JS	DWG T870005	REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED