

## SUMMARY

### # Wires

Low voltage 5



*Image is for illustrative purpose only*

|                  |                                    |
|------------------|------------------------------------|
| Series           | OK                                 |
| Termination type | Female crimp                       |
| IP rating        | 68                                 |
| AWG wire size    | 26.00 - 22.00                      |
| Cable Ø          | 0.00 - 0.00 mm                     |
| Status           | active                             |
| Matching parts   | <a href="#">FGG.0K.305.CYCC50Z</a> |

### Download

[Request a quote](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

|                   |                                                                                                                               |
|-------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Shell Style/Model | EE*: Fixed receptacle, nut fixing (back panel mounting)                                                                       |
| Keying            | 1 key (alpha=0, plug: male contacts, receptacle: female contacts)                                                             |
| Housing Material  | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Weight            | 13.17 g                                                                                                                       |

### Performance

|               |                            |
|---------------|----------------------------|
| Configuration | OK.305 : 5 Low Voltage     |
| Insulator     | Y: PEEK for crimp contacts |
| Rated Current | 6.5 Amps                   |

### Specifications

|                                                 |
|-------------------------------------------------|
| Contact Type: Crimp                             |
| Contact Retention: 22 N                         |
| Contact Dia.: 0.7 mm (0.028in)                  |
| Bucket Dia.: 0.8 mm (0.031in)                   |
| Min. Conductor: 0.14 mm <sup>2</sup> (AWG 26)   |
| Max. Conductor: 0.34 mm <sup>2</sup> (AWG 22)   |
| R (max): 6.1 mOhm                               |
| Vtest (contact-shell): 1200 V (AC), 1700 V (DC) |


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Vtest (contact-contact): 1250 V (AC), 1770 V (DC)

Others

- Endurance (Shell): 5000 mating cycles
- Temp (min / max): -55°C / +200°C
- Humidity (max): <=95% [at 60 deg C / 140 F]
- Vibration: 15 g [10 Hz - 2000 Hz]
- Shock Resistance: 100 g [ 6 ms]
- Climatical Category: 50/175/21
- Shielding (min): 95 dB (10 MHz)
- Shielding (min): 80 dB (1 GHz)
- Salt Spray Corrosion: >1000 hr

DRAWINGS



Dimensions

|     | A    | B    | E    | L    | M    | N    | P    | S1   | e       |
|-----|------|------|------|------|------|------|------|------|---------|
| mm. | 18   | 18   | 3.4  | 21.7 | 3.5  | 20.1 | 7    | 12.5 | M14x1.0 |
| in. | 0,71 | 0,71 | 0,13 | 0,85 | 0,14 | 0,79 | 0,28 | 0,49 |         |

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Crimp Tool: [DPC.91.701.V](#)


Crimp settings: AWG/Selector = 22-24-26/6-5-5

Positionner: [DCE.91.070.BVM](#)

Extractor: [DCF.92.070.3LT](#)

Replacement contact: EGG.0B.655.ZZM

### Cables

|                    |               |       |                                                                                     |
|--------------------|---------------|-------|-------------------------------------------------------------------------------------|
| CMN.05.T22.051QGZE | TPR (medical) | Grey  |  |
| CMN.05.T28.029PGCE | PVC           | GREY  |  |
| CMN.05.T28.029PGZE |               | Grey  |  |
| CMN.05.T28.029PNCE | PVC           | Black |  |
| CMN.05.T28.029PNZE |               |       |  |
| 150250             | PVC           | Grey  |  |
| 50090              | PVC           | Black |                                                                                     |
| 50140              | PVC           | Grey  |  |
| 5050               | PVC           | Black |  |

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.