


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	REV PER ECN-22-150900	28APR2022	RK	CSD

AMP WIRE RANGE
12-10 AWG STRANDED

1 WIRE INSULATION DIA .150 TO ..220.

2 FINISH: BODY AND SLEEVE:
TIN PLATE PER ASTM B545.

3 MATERIAL: BODY AND SLEEVE,
COPPER PER ASTM B152
INSULATION: PVF²
COLOR- NATURAL



500	LOOSE PIECE	696429-1
QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 150°C		THIS DRAWING IS A CONTROLLED DOCUMENT.		TE Connectivity		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: —	DIMENSIONS: INCHES 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± .008 3 PLC ± — 4 PLC ± — ANGLES ± —	DWN JR RUTH 19AUG05		
	TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] STRANDED			CHK T MICHIELUTTI 19AUG05		
FOR APPLICATION TOOLING INFORMATION	1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL — 	FINISH — 	APVD T MICHIELUTTI 19AUG05	
						NAME SPLICE, BUTT, PVF2 , P.I.D.G. WIRE SIZE: 12-10 AWG		
						PRODUCT SPEC —		
						APPLICATION SPEC —		
						WEIGHT —		
						SIZE A3		
						CAGE CODE 00779		
						DRAWING NO C-696429		
						RESTRICTED TO —		
						CUSTOMER DRAWING		
						SCALE 1:1		
						SHEET 1 OF 1		
						REV A2		