





P	LTR	DESCRIPTION	DATE	DWN	APVD
	M1	REVISED PER ECR-23-167167	13MAR2023	BB	MF



- | | |
|---|--|
| 1 | [-Y-] SHALL BE THE INTERSECTION OF THE POST AND HOUSING |
| 2 | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING. |
| 3 | 0.00254[.000100]-0.00508[.000200] MATTE TIN-LEAD OVER 0.00127[.000050] NICKEL ENTIRE POST. |
| 4 | HOUSING: LCP, COLOR-BLACK.
POST: COPPER ALLOY.
PICK AND PLACE CAP: PPA, COLOR-BLACK. |
| 5 | PACKAGED IN TAPE AND REEL PER EIA-481 SPECIFICATIONS.
SEE TABLE FOR TAPE WIDTHS. |
| 6 | PRELIMINARY PART NUMBER - NOT RELEASED FOR PRODUCTION |
| 7 | 0.00254[.000100]-0.00508[.000200] MATTE TIN OVER 0.00127[.000050] NICKEL ENTIRE POST. |



RECOMMENDED PCB LAYOUT
FOR USE WITH 0.20[.008] THICK STENCIL

VER	6	7	56MM	35.56 [1.400]	14	37.69 [1.484]	15	6-147291-3
	6	7	56MM	33.02 [1.300]	13	35.15 [1.384]	14	6-147291-2
	6	7	56MM	30.48 [1.200]	12	32.61 [1.284]	13	6-147291-1
	6	7	56MM	25.4 [1.000]	10	27.53 [1.084]	11	6-147291-0
	6	7	56MM	22.86 [.900]	9	24.99 [.984]	10	5-147291-9
	6	7	32MM	10.16 [.400]	4	12.29 [.484]	5	5-147291-8
	6	7	32MM	12.70 [.500]	5	14.83 [.584]	6	5-147291-7
	6	7	24MM	7.26 [.300]	3	9.75 [.384]	4	5-147291-6
		7	24MM	5.08 [.200]	2	7.21 [.284]	3	5-147291-5
		7	56MM	27.94 [1.100]	11	30.07 [1.184]	12	5-147291-4
	6	7	44MM	20.32 [.800]	8	22.45 [.884]	9	5-147291-3
	6	7	44MM	17.78 [.700]	7	19.91 [.784]	8	5-147291-2
		7	44MM	15.24 [.600]	6	17.37 [.684]	7	5-147291-1
	6	3	24MM	7.26 [.300]	3	9.75 [.384]	4	147291-6
	6	3	24MM	5.08 [.200]	2	7.21 [.284]	3	147291-5
OBSOLETE		3	56MM	27.94 [1.100]	11	30.07 [1.184]	12	147291-4
	6	3	56MM	22.58 [.900]	9	27.53 [1.084]	10	147291-3
	6	3	44MM	17.78 [.700]	7	19.91 [.784]	8	147291-2
OBSOLETE		3	44MM	15.24 [.600]	6	17.37 [.684]	7	147291-1
	PLATING	TAPE WIDTH	C	B	A	NO. OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER 14/JUN/99	 TE Connectivity	
		CHK J. GESFORD 14/JUN/99		
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SMT HDR ASSY, MOD II, BRKAWAY, VT, SNGL ROW, .100X.100 CL, .025SQ POST, PNP CAP —
		APVD J. GESFORD 14/JUN/99		
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.13 [.005] 4 PLC ± — ANGLES ± —		PRODUCT SPEC — APPLICATION SPEC —		
MATERIAL 		WEIGHT —		
FINISH SEE TABLE		SIZE A2		CAGE CODE —
		DRAWING NO C-147291		RESTRICTED TO —
		CUSTOMER DRAWING		SCALE 5:1 SHEET 1 of 1 REV M1