







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
1		INITIAL RELEASE	13SEP2013	RG	AC
2		REVISED PER ECO-14-018993	24PR2015	RG	MC



ISOMETRIC VIEW
SCALE 5:1





- 1 SURFACE TRACES PERMITTED WITHIN THIS LENGTH EXCEPT WHERE CAGE STANDOFFS, SHOWN IN DETAIL J, CONTACT PC BOARD.
- 2 MINIMUM PITCH DIMENSION.
3. MATES WITH QSFP MSA COMPATIBLE TRANSCEIVER.
- 4 REFERENCE APPLICATION SPEC 114-13218 FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- 5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMERS.
- 6 DIMENSION C IS THE NOMINAL THICKNESS OF CUSTOMER SUPPLIED PC BOARD,
SINGLE SIDED PC BOARD MINIMUM THICKNESS: 1.45
- 7 DATUM -A- IS TOP SURFACE OF THE HOST BOARD.
- 8 DATE CODE (YYWWD) MARKED APPROXIMATELY AS SHOWN.
- 9 CAGE MATERIAL: 0.25 THICK COPPER ALLOY
EMI SPRING MATERIAL: COPPER ALLOY
FRONT FLANGE MATERIAL: ZINC ALLOY.
- 10 EMI SPRING FINISH: 2µm TIN
FRONT FLANGE FINISH: 3µm MIN THICK TIN OVER 1.27µm
MIN THICK NICKEL OVER 5.08µm
MIN THICK COPPER.



2170396-1
PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ROBERT GAN 13SEP2013	TE Connectivity	
		CHK JASON YANG 13SEP2013		
DIMENSIONS:		APVD ALEX CAI 13SEP2013	NAME	
mm		PRODUCT SPEC	CAGE ASSEMBLY, BEHIND BEZEL, QSFP	
		108-2286		
		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO	
		114-13218		
MATERIAL		WEIGHT	A100779C=2170396	
		Customer Drawing		
		SCALE 2:1	SHEET 1 OF 3	
			REV 2	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ROBERT GAN 13SEP2013	TE Connectivity	
		CHK JASON YANG 13SEP2013		
DIMENSIONS:		APVD AILEY CAI 13SEP2013	NAME CAGE ASSEMBLY, BEHIND BEZEL, QSFP	
mm		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO	
		108-2286	RESTRICTED TO	
		APPLICATION SPEC	A100779C=2170396	
		114-13218	SCALE 2:1 SHEET 2 OF 3 REV 2	
MATERIAL		WEIGHT	Customer Drawing	
-		-		
-		-		

