

SUMMARY

Wires

Low voltage 14



Image is for illustrative purpose only

Series	2W
Termination type	Female solder
IP rating	68
AWG wire size	30.00 - 22.00
Cable Ø	0.00 - 0.00 mm
Status	active
Matching parts	FVG.2W.314.CLAC50

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	EV*: Fixed socket, nut fixing
Keying	1 key (alpha=0; Plug: male contacts; Receptacle: female contacts)
Housing Material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Weight	24.75 g

Performance

Configuration	2W.314 : 14 Low Voltage
Insulator	
Rated Current	6.5 Amps

Specifications


Contact Type: Solder
Contact Dia.: 0.7 mm (0.028in)
Bucket Dia.: 0.8 mm (0.031in)
Max. Solid Conductor: 0.34 mm² (AWG 22)
Max. Stranded Conductor: 0.34 mm² (AWG 22)
R (max): 6.1 mOhm
Vtest (contact-contact): 1150 V (AC) 1600 V (DC)
Vtest (contact-shell): 1350 V (AC) 1900 V (DC)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Others

- Endurance (Shell): 1000 mating cycles
- Temp (min / max): -20°C / +200°C
- Humidity (max): <=95% [at 60 deg C / 140 F]
- Climatical Category: 20/200/21
- Shielding (min): 95 dB (10 MHz)
- Shielding (min): 80 dB (1 GHz)
- Salt Spray Corrosion: >1000 hr
- Pressure: 30 bars

DRAWINGS



Dimensions


	A	B	E	L	N	S1	S2	S3	e	e1
mm.	22.5	21.8	9	30.7	9	14.5	18.5	19	M16x1.0	M20x1.0
in.	0,89	0,86	0,35	1,21	0,35	0,57	0,73	0,75		

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

CMN. 14.T22.068PGCE	PVC	GREY	
CMN. 14.T22.068PGZE		Grey	
CMN. 14.T22.068PNCE	PVC	Black	
CMN. 14.T22.068PNZE			
CMN. 14.T28.056PGZE		Grey	
CMN. 14.T28.056PNZE			
CMN. 14.T28.056QGZE	TPR (medical)	Grey	
114260	PTFE	White	
214140	PVC	Black	
214240	PTFE	White	
314250	PVC	Grey	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.