


Item number: GG1L0C-P06QF00-0000



ODU MINI-SNAP[®] devices Part

6 poles


- use Part

chrome Matt: Housing

Remember the product


[Download PDF](#)

(Example: image representation of the design)



Dimensions

Number of poles: 6 poles



contact insert

6-pin

socket

PCB contact (PCB)

Coding 0 °



Insulation material:	PEEK
Contact diameter:	0
Cable diameter:	from 0 mm to 0 mm
Max. Connection cross section:	kA / kA mm ²
Connection	diameter : 0 mm

Technical specifications

Continuity resistance	:	kA	μΩ
Insulation resistance:	10 ^ 16 Ω		
Air and creepage distance:	0 mm	according to IEC 60664-1: 2007 (VDE 0110-1: 2008)	
Current load Single contact:	0 A		
Current load compl. Application:	0 A	VDE 0298-4: 2013	
Test		voltage:	0 kV SAE AS 13441: 2004 method 3001.1
Rated voltage:	0 kV	SAE AS 13441: 2004 method 3001.1	

All dimensions in mm. All illustrations are illustrations. Subject to change.

General information about ODU MINI-SNAP Application

temperature: -40 ° C to + 120 ° C

ODU GmbH & Co. KG

Pregelstraße 11
84453 Mühldorf / Inn

Tel: +49 8631 6156-0
Fax: +49 8631 6156-49
E-Mail: central@odu.de

Print date 15.09.2017