

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION					
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.				ALL INTERNATIONAL RIGHTS RESERVED.					
LOC		DIST		REVISIONS					
G		86		P	LTR	DESCRIPTION	DATE	DWN	APVD
					F	REVISED PER ECO-10-013908	07JUL10	PY	BW

15.88 R
[.625]
MAX WASHER

INSERT

BRAZED SEAM

26.77
[1.054]
MAX DIA

18.31
[.721]
MIN DIA

50.47
[1.987]
MAX

66.09
[2.602]
MAX

36.22
[1.426]
MAX

'A' ±0.13
[±.005] DIA
FOR 'B' STUD
SEE TABLE BELOW

BODY


1

1

STAMP AMP 250-300 MCM APPROX AS SHOWN

MATERIAL THK: 3.20 ±0.10 [1.26 ±.004]

OBSOLETE	16.66 [.656]	5/8	BODY: COPPER PER ASTM B-152 ANNEALED	52559-5
	13.08 [.515]	1/2	TIN PL 0.00254 [.000100] MIN THK PER MIL-T-10727	52559-4
OBSOLETE	11.51 [.453]	7/16		52559-3
	9.91 [.390]	3/8	INSERT: BRASS PER MIL-C-50	52559-2
OBSOLETE	8.33 [.328]	5/16	TIN PL 0.00254 [.000100] MIN THK PER MIL-T-10727	52559-1
	6.73 [.265]	1/4		52559
	'A'	'B'	6.73 [.265]	PART NO

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 08MAR95	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
VOLTAGE RATING: NOT APPLICABLE	DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK AJ KAUFMAN 09MAR95	NAME	
WIRE CROSS SECTIONAL AREA RANGE: 117.0-152.0 mm [231-300] MCM SOLID OR STRANDED		0 PLC ± -	APVD RE ROSER 09MAR95	TERMINAL, RING TONGUE, STRANDED/SOLID, COPALUM WIRE SIZE: 250-300 MCM	
		1 PLC ± -	PRODUCT SPEC JL MECKLEY 09MAR95	SIZE	
		2 PLC ± -	APPLICATION SPEC	CAGE CODE	DRAWING NO
		3 PLC ± -	WEIGHT	RESTRICTED TO	
		4 PLC ± -		A300779C-52559	
		ANGLES ± -		SCALE 1:1	
		FINISH		SHEET 1 OF 1	
	SEE TABLE	SEE TABLE	CUSTOMER DRAWING		REV F