


RS VERT 4P 20X4 S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Distributor module with 4 voltage potentials
(P1,P2,P3,P4) in 20P1,20P2,20P3 and 20P4 for tension-
clamp or screw connection.

General ordering data

Version	Interface, RS VERT, 4 P, Screw connection
Order No.	1128100000
Type	RS VERT 4P 20X4 S
GTIN (EAN)	4032248909735
Qty.	1 pc(s).

RS VERT 4P 20X4 S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	55 mm	Depth (inches)	2.165 inch
Height	70 mm	Height (inches)	2.756 inch
Width	145 mm	Width (inches)	5.709 inch
Net weight	350 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1	SCIP	3820ceea-2b49-4a61-bda5-08f3867b3419
------------	----------------	------	--------------------------------------

Connection data

Distribution PCB connectors	LL2N 5.08 mm	Number of potentials	4
Supply plug-in connectors	TOP 1.5GS2/180		

Rating data

Rated voltage	< 600 V AC	Operating voltage	< 600 V AC
Maximum current per potential connection	30 A	Maximum current per distributor connection	15 A
Total operating current	120 A		

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 600 V AC
Surge voltage category	III	Pollution severity level	2
Pulse voltage test (1,2/50µs)	6 kV	Insulation test voltage	1.65 kVAC

Connection field

Clamping range, max.	6 mm ²	Clamping range, min.	0.13 mm ²
Flexible with sleeve, max.	2.5 mm ²	Flexible with sleeve, min.	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Max. wire cross-section, AWG	AWG 12	Min. wire cross-section, AWG	AWG 26
Sleeve with plastic collar, max.	2.5 mm ²	Solid, max. H05(07) V-U	6 mm ²
Solid, min. H05(07) V-U	0.5 mm ²	Stripping length	6 mm
Tightening torque, max.	0.6 Nm	Tightening torque, min.	0.5 Nm
Type of connection	Screw connection		

Supply connection

Type of connection	Screw connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²	Solid, min. H05(07) V-U	0.5 mm ²
Solid, max. H05(07) V-U	6 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible with sleeve, max.	4 mm ²
Flexible with sleeve, min.	0.5 mm ²	Ferrule with plastic collar, max.	4 mm ²
Wire cross-section, min. AWG	AWG 26	Wire cross-section, max. AWG	AWG 10
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm
Stripping length	13 mm		

RS VERT 4P 20X4 S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ECLASS 9.0	27-14-11-52
ECLASS 9.1	27-14-11-52	ECLASS 10.0	27-14-11-52
ECLASS 11.0	27-14-11-52	ECLASS 12.0	27-14-11-52

Approvals

Approvals



ROHS

Conform

DownloadsApproval/Certificate/Document of
Conformity[Declaration of Conformity](#)

Product Change Notification

[20211027 Technical change to RS VERT interfaces](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

RS VERT 4P 20X4 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

