



DEUTSCH

TE Internal #: ZPF000000000104271  
Rectangular Contact Inserts, Pin, Pin, Contact Insert Pole Configuration 12, Wire-to-Board, 12 Position, 3.38mm [.13in] Centerline, Sealable

[View on TE.com >](#)

Connectors > Rectangular Connectors > Rectangular Contact Inserts



Rectangular Connector Insert Type: **Pin**  
Contact Type: **Pin**  
Contact Insert Pole Configuration: **12**  
Connector System: **Wire-to-Board**  
Number of Positions: **12**

Features

Product Type Features

Product Type	Module
Rectangular Connector Insert Type	Pin
Connector System	Wire-to-Board
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	12
---------------------	----

Body Features

Module Material	Composite
-----------------	-----------

Contact Features

Contact Type	Pin
Contact Insert Pole Configuration	12
Contact Current Rating (Max)	7.5 A

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	3.38 mm [.13 in]
--------------------	------------------



Usage Conditions

Operating Temperature Range	-55 – 175 °C[-67 – 347 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power, Signal & Data
---------------------	----------------------

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Pb (1.2% in alloy) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought





TE Part #3-1630019-5

Power Resistors: Aluminum Housed, HSA



TE Part #2273115-5

M12 MS-FS DOUBLE END CABLE ASSY BL



TE Part #2273034-3

M12 A-CODE MALE STRAIGHT PIGTAIL



TE Part #2-1879448-5

Wirewound Resistor: Mineral, 2.5 Kw




TE Part #132072-2

TERMINAL STRATO THERM RING, 2 AWG, M10



TE Part #2344657-8

FPC ANTENNA, CABLE, MHF, Wi-Fi TRIPLE



TE Part #33195

TERMINAL,BUDG R 16-14 1/4



TE Part #36485

PIDG RING TONGUE TERMINALS



TE Part #ZPF000000000122608

732-8256-20



TE Part #1742881-1

250 FAST FLG RCPT AMVAR TPBR

Documents

Product Drawings

732-8254-20

English

Datasheets & Catalog Pages

DEUTSCH DMC-M Series Multicavity EN4165 Connectors

English

DMC-M Series Single Module EN4165

English