

FP BOX 10P**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



The FieldPower® power distributors support error-free installation in an extremely short space of time. Branches and functions integrated in the cover can simply be plugged in. Robust with high protection degree.

General ordering data

Order No.	1957590000
Type	FP BOX 10P
GTIN (EAN)	4032248636662
Qty.	1 pc(s).

FP BOX 10P

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Depth	67 mm	Depth (inches)	2.638 inch
Height	181 mm	Height (inches)	7.126 inch
Width	192 mm	Width (inches)	7.559 inch
Net weight	950 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...55 °C
---------------------	----------------	-----------------------	----------------

Environmental Product Compliance

REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3	SCIP	5f19cd84-8946-4797-9386-3ac323b
------------	--	------	---------------------------------

Clamping capacity, IDC connection - PT6

Blade size	0.6 x 3.5 mm	Connection cross-section, finely stranded, max.	6 mm ²
Connection cross-section, finely stranded, min.	2.5 mm ²	Connection cross-section, stranded, max.	6 mm ²
Connection cross-section, stranded, min.	2.5 mm ²	Wire connection cross section, finely stranded, max.	6 mm ²
Wire connection cross section, finely stranded, min.	2.5 mm ²	Wire cross-section, solid, max.	6 mm ²

Clamping capacity, PUSH IN connection - PT6

Blade size	0.6 x 3.5 mm	Blade size, PUSH IN connection	0.6 x 3.5 mm
Cross-section for connected wire PUSH IN connection, solid, min.	0.5 mm ²	Cross-section for connected wire, PUSH IN connection, solid, max.	6 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/1, PUSH IN connection, max.	6 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/1, PUSH IN connection, min.	0.5 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/4, PUSH IN connection, max.	6 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 12mm with plastic collar, DIN 46228/4, PUSH IN connection, min.	0.5 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/1, PUSH IN connection, max.	6 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/1, PUSH IN connection, min.	0.5 mm ²
Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/4, PUSH IN connection, max.	6 mm ²	Cross-section for connected wire, flexible with wire-end ferrules, 8mm with plastic collar, DIN 46228/4, PUSH IN connection, min.	0.5 mm ²
Cross-section for connected wire, flexible, PUSH IN connection, max.	10 mm ²	Cross-section for connected wire, flexible, PUSH IN connection, min.	0.5 mm ²
Finely-stranded flexible, max. PUSH IN connection	6 mm ²	Finely-stranded flexible, min. PUSH IN connection	0.5 mm ²
Stripping length, PUSH IN connection	14 mm	Wire connection cross section, stranded, PUSH IN connection, max.	6 mm ²
Wire connection cross section, stranded, PUSH IN connection, min.	0.5 mm ²		

FP BOX 10P

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

Technical data

info@weidmueller.com

www.weidmueller.com

General information #96 connectors

Can be coded	Yes, Coded on PE	Number of connections / poles	10
Type of mounting	Screw mounting	UL 94 flammability rating	5VA
lockable	No		

General data

Can be coded	Yes, Coded on PE	Material	Polycarbonate, glass fibre reinforced
Protection degree	IP65	Silicone	No
UL 94 flammability rating	5VA		

Dimensions of box

Height	181 mm	Width	192 mm
--------	--------	-------	--------

Rated data acc. to IEC

Rated cross-section	6 mm ²	Rated current	41 A
Rated impulse withstand voltage	8 kV	Rated voltage	800 V
Standards	UL 2237, DIN EN 60947-7-1, DIN EN 60947-7-2		

Rated data acc. to UL

Note	For use with UL-listed TC-ER cables	Rated current (Use group D / UL 1059)	30 A
Rated voltage (Use group D / UL 1059)	600 V	Standards	UL 2237, DIN EN 60947-7-1, DIN EN 60947-7-2
Wire connection cross section AWG, max.	AWG 10	Wire connection cross section AWG, min.	AWG 14

Classifications

ETIM 6.0	EC000214	ETIM 7.0	EC000214
ETIM 8.0	EC000214	ECLASS 9.0	27-14-24-09
ECLASS 9.1	27-14-24-09	ECLASS 10.0	27-14-24-09
ECLASS 11.0	27-14-24-09	ECLASS 12.0	27-14-24-09

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UL)	E310075

FP BOX 10P

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

Technical data

info@weidmueller.com

Downloads

Approval/Certificate/Document of Conformity	UL Certificate FieldPower® Box and accessories Manufacturer's Declaration FieldPower® BOX, BOX FUSE and Terminal variants	www.weidmueller.com
Engineering Data	CAD data – STEP	
Engineering Data	WSCAD	
Product Change Notification	Produktänderungsmitteilung FieldPower® Box Schrauben Product Change Notification FieldPower® box screws	
User Documentation	Manual FieldPower® Box	
Catalogues	Catalogues in PDF-format	

FP BOX 10P

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

Drawings

Drilling template

