

## Description

The AH3762Q is an AEC-Q100 qualified high-voltage, high-sensitivity Hall-Effect latch IC designed for brushless DC-motor commutation speed measurement, angular or linear encoders and position sensors in automotive applications. To support a wide range of demanding applications, the design is optimized to operate over the supply range of 3.0V to 28V. With chopper stabilized architecture and an internal bandgap regulator to provide temperature compensated supply for internal circuits, the AH3762Q provides a reliable solution over the whole operating range. For robustness and protection, the device has a reverse blocking diode with a Zener clamp on the supply. The output has an overcurrent limit and a Zener clamp.

The single, open-drain output can be switched on with South pole of sufficient strength and switched off with North pole of sufficient strength. When the magnetic flux density (B) perpendicular to the package is larger than the operate point (Bop) the output is switched on (pulled low). The output is held latched until magnetic flux density reverses and becomes lower than the release point (Brp).

The magnetic operating and release polarity is opposite for SOT23 and SC59 packages. SOT23 and SIP-3 (Ammo Pack), SIP-3 (Bulk Pack) packages will require south pole to the part marking side to operate while SC59 will require south pole to the non part-marking side.



## Features

- Bipolar Latch Operation (South Pole: On, North Pole: Off)
- High Sensitivity: Bop and Brp of +25G and -25G Typical
- Single Open-Drain Output with Overcurrent Limit
- 3.0V to 28V Operating Voltage Range
- Chopper Stabilized Design Provides
  - Superior Temperature Stability
  - Minimal Switch Point Drift
  - Enhanced Immunity to Stress
- Good RF Noise Immunity
- Reverse Blocking Diode
- Zener Clamp on Supply and Output Pins
- -40°C to +150°C Operating Temperature
- ESD: HBM > 8kV, CDM > 2kV
- AEC-Q100 Grade 0 Qualified
- Industry Standard SC59, SOT23 and SIP-3 (Ammo Pack), SIP-3 (Bulk Pack) Packages
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green Device (Note 3)**
- **The AH3762Q is suitable for automotive applications requiring specific change control; this part is AEC-Q100 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.**

<https://www.diodes.com/quality/product-definitions/>

- Notes:
1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
  2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
  3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.


## Pin Assignments



## Applications

- Brushless DC-Motor Commutation
- Revolution Per Minute (RPM) Measurement
- Angular and Linear Encoder and Position Sensing and Indexing
- Flow Meters
- Contactless Commutation, Speed Measurement and Angular Position Sensing/Indexing in Automotive Applications

## Typical Applications Circuit (Note 4)




Note: 4.  $C_{IN}$  is for power stabilization and to strengthen the noise immunity, the recommended capacitance is 10nF to 100nF.  $R_L$  is the pull-up resistor.

## Pin Descriptions

Package: SC59, SOT23 and SIP-3 (Ammo Pack), SIP-3 (Bulk Pack)

| Pin Number | Pin Name        | Function           |
|------------|-----------------|--------------------|
| 1          | V <sub>DD</sub> | Power Supply Input |
| 2          | GND             | Ground             |
| 3          | OUTPUT          | Output Pin         |

## Functional Block Diagram



## Absolute Maximum Ratings (Notes 5 and 6) (@T<sub>A</sub> = +25°C, unless otherwise specified.)

| Symbol               | Characteristic                                                 | Value                                   | Unit |
|----------------------|----------------------------------------------------------------|-----------------------------------------|------|
| V <sub>DD</sub>      | Supply Voltage (Note 6)                                        | 32                                      | V    |
| V <sub>DDR</sub>     | Reverse Supply Voltage (Note 6)                                | -32                                     | V    |
| V <sub>OUT_MAX</sub> | Output Off Voltage (Note 6)                                    | 32                                      | V    |
| I <sub>OUT</sub>     | Continuous Output Current                                      | 60                                      | mA   |
| I <sub>OUT_R</sub>   | Reverse Output Current                                         | -50                                     | mA   |
| B                    | Magnetic Flux Density                                          | Unlimited                               |      |
| P <sub>D</sub>       | Package Power Dissipation                                      | SIP-3 (Ammo Pack),<br>SIP-3 (Bulk Pack) | mW   |
|                      |                                                                | SC59 and SOT23                          |      |
|                      |                                                                | 550                                     |      |
| T <sub>S</sub>       | Storage Temperature Range                                      | -65 to +165                             | °C   |
| T <sub>J</sub>       | Maximum Junction Temperature                                   | +150                                    | °C   |
| ESD HBM              | Electrostatic Discharge Withstand – Human Body Model (HBM)     | 8                                       | kV   |
| ESD MM               | Electrostatic Discharge Withstand - Machine Model (MM)         | 800                                     | V    |
| ESD CDM              | Electrostatic Discharge Withstand - Charged Device Model (CDM) | 2                                       | kV   |

- Notes:
- Stresses greater than the 'Absolute Maximum Ratings' specified above can cause permanent damage to the device. These are stress ratings only; functional operation of the device at these or any other conditions exceeding those indicated in this specification is not implied. Device reliability can be affected by exposure to absolute maximum rating conditions for extended periods of time.
  - The absolute maximum V<sub>DD</sub> of 32V is a transient stress rating and is not meant as a functional operating condition. It is not recommended to operate the device at the absolute maximum rated conditions for any period of time.

## Recommended Operating Conditions (@T<sub>A</sub> = -40°C to +150°C, unless otherwise specified.)

| Symbol          | Parameter                   | Conditions | Rating      | Unit |
|-----------------|-----------------------------|------------|-------------|------|
| V <sub>DD</sub> | Supply Voltage              | Operating  | 3.0 to 28   | V    |
| T <sub>A</sub>  | Operating Temperature Range | Operating  | -40 to +150 | °C   |

## Electrical Characteristics (Notes 7 and 8) (@T<sub>A</sub> = -40°C to +150°C, V<sub>DD</sub> = 3V to 28V, unless otherwise specified.)

| Symbol              | Parameter                                                                                          | Conditions                                             | Min | Typ  | Max   | Unit |
|---------------------|----------------------------------------------------------------------------------------------------|--------------------------------------------------------|-----|------|-------|------|
| V <sub>OUT_ON</sub> | Output ON Voltage                                                                                  | I <sub>OUT</sub> = 20mA, B > Bop                       | —   | 0.2  | 0.4   | V    |
| I <sub>LKG</sub>    | Output Leakage Current (When Output is Off)                                                        | V <sub>OUT</sub> = 28V, B < Brp, Output Off            | —   | <0.1 | 10    | μA   |
| I <sub>DD</sub>     | Supply Current                                                                                     | Output Open, T <sub>A</sub> = +25°C                    | —   | 3    | 3.5   | mA   |
|                     |                                                                                                    | Output Open, T <sub>A</sub> = -40 to +150°C            | —   | —    | 4     | mA   |
| I <sub>DD_R</sub>   | Reverse Supply Current                                                                             | V <sub>DD</sub> = -18V, T <sub>A</sub> = +25°C         | —   | 0.6  | —     | μA   |
|                     |                                                                                                    | V <sub>DD</sub> = -18V, T <sub>A</sub> = -40 to +150°C | —   | 0.6  | 1,500 | μA   |
|                     |                                                                                                    | V <sub>DD</sub> = -28V, T <sub>A</sub> = +25°C         | —   | 1.6  | —     | μA   |
|                     |                                                                                                    | V <sub>DD</sub> = -28V, T <sub>A</sub> = -40 to +150°C | —   | 1.6  | 2,500 | μA   |
| t <sub>P_ON</sub>   | Device Power-On Time (Start-Up Time)                                                               | V <sub>DD</sub> ≥ 3V, B > Bop (Note 8)                 | —   | 10   | —     | μs   |
| f <sub>c</sub>      | Chopping Frequency                                                                                 | V <sub>DD</sub> ≥ 3V                                   | —   | 800  | —     | kHz  |
| t <sub>d</sub>      | Response Time Delay (Time from Magnetic Threshold Reached to the Start of the Output Rise or Fall) | (Note 9)                                               | —   | 3.75 | —     | μs   |
| t <sub>r</sub>      | Output Rising Time (External Pull-Up Resistor R <sub>L</sub> and Load Capacitance Dependent)       | R <sub>L</sub> = 1kΩ, C <sub>L</sub> = 20pF            | —   | 0.2  | 1     | μs   |
| t <sub>f</sub>      | Output Falling Time (Internal Switch Resistance and load capacitance dependent)                    | R <sub>L</sub> = 1kΩ, C <sub>L</sub> = 20pF            | —   | 0.1  | 1     | μs   |
| I <sub>OCL</sub>    | Output Current Limit                                                                               | B > Bop (Note 10)                                      | 30  | —    | 55    | mA   |
| V <sub>Z</sub>      | Zener Clamp Voltage                                                                                | I <sub>DD</sub> = 5mA                                  | 28  | —    | —     | V    |



- Notes:
- When power is initially turned on, V<sub>DD</sub> must be within its correct operating range (3.0V to 28V) to guarantee the output sampling. The output state is valid after the start-up time of 10μs typical from the operating voltage reaching 3V.
  - Typical values are defined at T<sub>A</sub> = +25°C, V<sub>DD</sub> = 12V. Maximum and minimum values over the operating temperature range are not tested in production but guaranteed by design, process control and characterization.
  - Guaranteed by design, process control and characterization. Not tested in production.
  - The device will limit the output current I<sub>OUT</sub> to current limit of I<sub>OCL</sub>.

**Magnetic Characteristics** (Notes 11 and 12) ( $T_A = -40^\circ\text{C}$  to  $+150^\circ\text{C}$ ,  $V_{DD} = 3.0\text{V}$  to  $28\text{V}$ , unless otherwise specified.)

(1mT=10 Gauss)





| Symbol                                                                                                                                                                            | Parameter            | Conditions                                        | Min | Typ | Max | Unit  |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------|---------------------------------------------------|-----|-----|-----|-------|
| Bop (South pole to part marking side for SOT23 and SIP-3 (Ammo Pack), SIP-3 (Bulk Pack) packages;<br>South pole to the non-part marking side for SC59 package. See diagram below) | Operation Point      | $V_{DD} = 12\text{V}$ , $T_A = +25^\circ\text{C}$ | —   | 25  | —   | Gauss |
|                                                                                                                                                                                   |                      | $T_A = -40^\circ\text{C}$ to $+150^\circ\text{C}$ | 10  | 25  | 40  |       |
| Brp (North pole to part marking side for SOT23 and SIP-3 (Ammo Pack), SIP-3 (Bulk Pack) packages;<br>North pole to the non-part marking side for SC59 package. See diagram below) | Release Point        | $V_{DD} = 12\text{V}$ , $T_A = +25^\circ\text{C}$ | —   | -25 | —   |       |
|                                                                                                                                                                                   |                      | $T_A = -40^\circ\text{C}$ to $+150^\circ\text{C}$ | -40 | -25 | -10 |       |
| $B_{HY}$ ( $ B_{opx}  -  B_{rpx} $ )                                                                                                                                              | Hysteresis (Note 13) | $V_{DD} = 12\text{V}$ , $T_A = +25^\circ\text{C}$ | —   | 50  | —   |       |
|                                                                                                                                                                                   |                      | $T_A = -40^\circ\text{C}$ to $+150^\circ\text{C}$ | 20  | 50  | 80  |       |

- Notes:
- When power is initially turned on,  $V_{DD}$  must be within its correct operating range (3.0V to 28V) to guarantee the output sampling. The output state is valid after the start-up time of 10 $\mu\text{s}$  typical from the operating voltage reaching 3V.
  - Typical values are defined at  $T_A = +25^\circ\text{C}$ ,  $V_{DD} = 12\text{V}$ . Maximum and minimum values over the operating temperature range is not tested in production but guaranteed by design, process control and characterization.
  - Maximum and minimum hysteresis is guaranteed by design, process control and characterization.





## Typical Operating Characteristics

### Output Switch Operate and Release Points (Magnetic Thresholds) – Bop and Brp





### Supply Current





## Typical Operating Characteristics (continued)



### Reverse Supply Current



### Output Switch On Voltage





### Output Switch Leakage Current



## Typical Operating Characteristics (continued)


### Output Current Limit



## Thermal Performance Characteristics


### (1) Package Type: SC59 and SOT23

| T <sub>A</sub> (°C) | 25  | 50  | 60  | 70  | 80  | 85  | 90  | 100 | 105 | 110 | 120 | 125 | 130 | 140 | 150 |
|---------------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| P <sub>D</sub> (mW) | 230 | 184 | 166 | 147 | 129 | 120 | 110 | 92  | 83  | 74  | 55  | 46  | 37  | 18  | 0   |




### (2) Package Type: SIP-3 (Ammo Pack), SIP-3 (Bulk Pack)

| T <sub>A</sub> (°C) | 25  | 50  | 60  | 70  | 80  | 85  | 90  | 100 | 105 | 110 | 120 | 125 | 130 | 140 | 150 |
|---------------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| P <sub>D</sub> (mW) | 550 | 440 | 396 | 362 | 308 | 286 | 264 | 220 | 198 | 176 | 132 | 110 | 88  | 44  | 0   |



## Ordering Information




| Part Number  | Status         | Package Code | Packaging                            | Bulk     |                    | 7" Tape and Reel  |                    | Ammo Box  |                    |
|--------------|----------------|--------------|--------------------------------------|----------|--------------------|-------------------|--------------------|-----------|--------------------|
|              |                |              |                                      | Quantity | Part Number Suffix | Quantity          | Part Number Suffix | Quantity  | Part Number Suffix |
| AH3762Q-P-A  | Active         | P            | SIP-3 (Ammo Pack), SIP-3 (Bulk Pack) | NA       | NA                 | NA                | NA                 | 4,000/Box | -A                 |
| AH3762Q-P-B  | Active         | P            | SIP-3 (Ammo Pack), SIP-3 (Bulk Pack) | 1,000    | -B                 | NA                | NA                 | NA        | NA                 |
| AH3762Q-SA-7 | NRND (Note 16) | SA           | SOT23                                | NA       | NA                 | 3,000/Tape & Reel | -7                 | NA        | NA                 |
| AH3762Q-W-7  | NRND (Note 16) | W            | SC59                                 | NA       | NA                 | 3,000/Tape & Reel | -7                 | NA        | NA                 |

Notes: 14. Ammo Box is for SIP-3 Spread Lead.  
 15. Bulk is for SIP-3 Straight Lead.  
 16. NRND = Not Recommended for New Design.

## Marking Information

### (1) Package Type: SC59 and SOT23

( Top View )




XX : Identification Code  
Y : Year 0 to 9  
W : Week : A to Z : 1 to 26 week;  
 a to z : 27 to 52 week; z represents 52 and 53 week  
X : Internal Code

| Part Number | Package | Identification Code |
|-------------|---------|---------------------|
| AH3762Q     | SC59    | YK                  |
| AH3762Q     | SOT23   | WK                  |

### (2) Package Type: SIP-3 (Ammo Pack), SIP-3 (Bulk Pack)

( Top View )




Y : Year : 0~9  
WW : Week : 01~52, "52" represents 52 and 53 week  
X : Internal Code

| Part Number | Package                              | Identification Code |
|-------------|--------------------------------------|---------------------|
| AH3762Q     | SIP-3 (Ammo Pack), SIP-3 (Bulk Pack) | 3762Q               |


## Package Outline Dimensions (All dimensions in mm.)

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

### (1) Package Type: SC59




| SC59                 |       |      |      |
|----------------------|-------|------|------|
| Dim                  | Min   | Max  | Typ  |
| A                    | 0.35  | 0.50 | 0.38 |
| B                    | 1.50  | 1.70 | 1.60 |
| C                    | 2.70  | 3.00 | 2.80 |
| D                    | -     | -    | 0.95 |
| G                    | -     | -    | 1.90 |
| H                    | 2.90  | 3.10 | 3.00 |
| J                    | 0.013 | 0.10 | 0.05 |
| K                    | 1.00  | 1.30 | 1.10 |
| L                    | 0.35  | 0.55 | 0.40 |
| M                    | 0.10  | 0.20 | 0.15 |
| N                    | 0.70  | 0.80 | 0.75 |
| α                    | 0°    | 8°   | -    |
| All Dimensions in mm |       |      |      |




# Package Outline Dimensions (continued) (All dimensions in mm.)

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

## (2) Package Type: SOT23



| SOT23                |       |       |       |
|----------------------|-------|-------|-------|
| Dim                  | Min   | Max   | Typ   |
| A                    | 0.37  | 0.51  | 0.40  |
| B                    | 1.20  | 1.40  | 1.30  |
| C                    | 2.30  | 2.50  | 2.40  |
| D                    | 0.89  | 1.03  | 0.915 |
| F                    | 0.45  | 0.60  | 0.535 |
| G                    | 1.78  | 2.05  | 1.83  |
| H                    | 2.80  | 3.00  | 2.90  |
| J                    | 0.013 | 0.10  | 0.05  |
| K                    | 0.890 | 1.00  | 0.975 |
| K1                   | 0.903 | 1.10  | 1.025 |
| L                    | 0.45  | 0.61  | 0.55  |
| L1                   | 0.25  | 0.55  | 0.40  |
| M                    | 0.085 | 0.150 | 0.110 |
| a                    | 0°    | 8°    | --    |
| All Dimensions in mm |       |       |       |




Sensor Location


## Package Outline Dimensions (continued) (All dimensions in mm.)

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

### (3) Package Type: SIP-3 (Bulk Pack)




| SIP-3 (Bulk Pack)    |          |       |       |
|----------------------|----------|-------|-------|
| Dim                  | Min      | Max   | Typ   |
| A                    | 1.40     | 1.60  | 1.50  |
| b                    | 0.33     | 0.43  | 0.38  |
| b2                   | 0.40     | 0.508 | 0.46  |
| c                    | 0.35     | 0.41  | 0.38  |
| D                    | 3.90     | 4.30  | 4.10  |
| E                    | 2.80     | 3.20  | 3.00  |
| e1                   | 1.24     | 1.30  | 1.27  |
| F                    | 0.00     | 0.20  | —     |
| J                    | 2.62 REF |       |       |
| L                    | 14.00    | 15.00 | 14.50 |
| L1                   | 1.55     | 1.75  | 1.65  |
| S                    | 0.63     | 0.84  | 0.74  |
| a1                   | —        | —     | 5°    |
| a2                   | —        | —     | 5°    |
| a3                   | —        | —     | 45°   |
| a4                   | —        | —     | 3°    |
| All Dimensions in mm |          |       |       |




Sensor Location

**Package Outline Dimensions** (continued) (All dimensions in mm.)

 Please see <http://www.diodes.com/package-outlines.html> for the latest version.

**(4) Package Type: SIP-3 (Ammo Pack)**



| SIP-3<br>(Ammo Pack) |          |       |       |
|----------------------|----------|-------|-------|
| Dim                  | Min      | Max   | Typ   |
| A                    | 1.40     | 1.60  | 1.50  |
| b                    | 0.33     | 0.43  | 0.38  |
| b2a                  | 0.40     | 0.52  | 0.46  |
| c                    | 0.35     | 0.41  | 0.38  |
| D                    | 3.90     | 4.30  | 4.10  |
| E                    | 2.80     | 3.20  | 3.00  |
| e1                   | 1.24     | 1.30  | 1.27  |
| e2                   | 2.40     | 2.90  | 2.65  |
| F                    | 0.00     | 0.20  | —     |
| J                    | 2.62 REF |       |       |
| L                    | 14.00    | 15.00 | 14.50 |
| La                   | 12.90    | 14.90 | 13.90 |
| L1                   | 1.55     | 1.75  | 1.65  |
| L3                   | 2.00     | 3.00  | 2.50  |
| S                    | 0.63     | 0.84  | 0.74  |
| a1                   | —        | —     | 5°    |
| a2                   | —        | —     | 5°    |
| a3                   | —        | —     | 45°   |
| a4                   | —        | —     | 3°    |
| All Dimensions in mm |          |       |       |



## Suggested Pad Layout


Please see <http://www.diodes.com/package-outlines.html> for the latest version.

### (1) Package Type: SC59



| Dimensions | Value (in mm) |
|------------|---------------|
| Z          | 3.4           |
| X          | 0.8           |
| Y          | 1.0           |
| C          | 2.4           |
| E          | 1.35          |

### (2) Package Type: SOT23



| Dimensions | Value (in mm) |
|------------|---------------|
| C          | 2.0           |
| X          | 0.8           |
| X1         | 1.35          |
| Y          | 0.9           |
| Y1         | 2.9           |

#### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

[www.diodes.com](http://www.diodes.com)