




LOC		DIST		REVISIONS					
AF		50		P	LTR	DESCRIPTION	DATE	DWN	APVD
					A1	REVISE PER ECR-14-002148, FASR APPROVED	13DEC2014	GRZ	JL

- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59±0.08 [.220±.003] CENTERS. SLOT TERMINATES A SINGLE MAGNET WIRE ONLY. COPPER RANGE: 0.90-1.15mm [#19-#17] AWG. ALUMINUM RANGE: 1.02-1.22mm [#18-#16.5] AWG, WITH CAVITY ANVIL HEIGHT TO BE 2.29±0.13 [.090±.005] FOR ALUMINUM WIRE ONLY.
- 2 AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° OR POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.
- 3 VARNISH RESIST OVER 0.002032 [.000080] MIN TIN PER MIL-T-10727.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	13NOV12	TE Connectivity			
DIMENSIONS: MM [INCHES]		CHK	LYONS LI	13NOV12				
		APVD	LYONS LI	13NOV12	NAME			
		PRODUCT SPEC			TERMINAL, TAB, 4.75 [.187] FASTON, MAG-MATE			
MATERIAL PREMILLED 4M BRASS		APPLICATION SPEC			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		114-2046			A2	00779	C=1742996	-
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT			SCALE		SHEET	REV
0 PLC ± -		-			10:1		1 of 1	A1
1 PLC ± -		CUSTOMER DRAWING						
2 PLC ± 0.25 [.010]								
3 PLC ± -								
4 PLC ± -								
ANGLES ± -								
FINISH								