

High Voltage Isolator

OPI1268



Features:

- TTL compatible output
- 16 kV dc isolation
- 2 Mbit/s
- $t_{PHL}-t_{PLH} \leq 500$ ns
- Creepage path: 0.970" (24.64 mm)
- Air path: 0.970" (24.64 mm)
- UL recognized file No. E58730



Description:

The **OPI1268** is a high voltage isolator with a digital output that is capable of high speed data transmission. The input of the OPI1268 consists of a high-efficiency GaAlAs LED with a peak wavelength of 850 nm, which is optically coupled to the output optical IC. A photodiode in the output IC detects the incoming modulated light and converts it to a proportionate current. This current is fed into a high-gain linear amplifier which is temperature, current and voltage compensated. The result is a highly stable digital output with an open collector inverter configuration. This device produces DC and AC voltage isolation between the input and output circuitry while providing TTL signal integrity.


Applications:

- Data transmission for High voltage isolation
- PCBoard power system isolation
- Industrial equipment power isolation
- Medical equipment power isolation
- Office equipment


Ordering Information

Part Number	LED Peak Wavelength	Sensor Photologic®	Isolation Voltage kVDC	t_{PLH} / t_{PHL} Max (ns)	I_f (mA) Typ / Max	V_{CE} (V) Max	Lead Length / Spacing
OPI1268	850 nm	Open Collector	16	100 / 200	10 / 50	18	0.14" / 0.98"

Pin	Function
1	Cathode
2	Anode
3	V_{CC}
4	Output
5	Ground



Pb-Free
(RoHS)



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

Electrical Specifications

Absolute Maximum Ratings ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Storage Temperature	-40° C to +100° C
Operating Temperature	-40° C to +100° C
Input-to-Output Isolation Voltage ⁽²⁾	16 kVDC
Lead Soldering Temperature (1/16" (1.6 mm) from case for 5 seconds with soldering iron) ⁽³⁾	260° C
Input Diode	
Continuous Forward Current	30 mA
Peak Forward current (1 μs pulse width, 300 pps)	3.0 A
Reverse Voltage	3.0 V
Power Dissipation ⁽¹⁾	100 mW
Output IC	
Maximum Supply Voltage	7 V
Power Dissipation ⁽⁴⁾	100 mW
Maximum Output Voltage	18 V
Maximum Output Current	25 mA

Electrical Characteristics ($T_A = 0^\circ\text{C}$ to 70°C unless otherwise noted)

SYMBOL	PARAMETER	MIN	TYP	MAX	UNITS	TEST CONDITIONS
Input Diode						
V _F	Forward Voltage	-	1.3	1.6	V	I _F = 20 mA
I _R	Reverse Current	-	0.1	100	μA	V _R = 2.0 V
Output IC (V _{CC} = 4.5 V to 5.25 V) (See OPL550 for additional information—for reference only.)						
I _{OH}	High Level Output Current	-	0.20	10	μA	I _F = 0.0 mA, V _{OH} = 18.0 V, V _{CC} = 5.25 V
V _{OL}	Low Level Output Voltage	-	0.44	0.55	V	I _F = 10.0 mA, I _{OL} = 8.0 mA, V _{CC} = 4.5 V
I _{CCH}	High Level Supply Current	-	4.2	7	mA	I _F = 0, V _{CC} = 5.25 V
I _{CCL}	Low Level Supply Current	-	6.7	10		I _F = 10.0 mA, V _{CC} = 5.25 V
Coupled Characteristics (V _{CC} = 5 V)						
C _{IO}	Coupling Capacitance	-	-	2	pF	Input and output leads shorted.
t _{PLH}	Propagation Delay to Low Output Level	-	-	200	ns	V _{CC} = 5 V, I _F = 30 mA, R _L = 560 Ω
t _{PHL}	Propagation Delay to High Output Level	-	-	100		
I _{ISO}	Isolation Leakage Current ⁽⁵⁾	-	-	20	μA	V _{ISO} = 19.2 kV dc
I _{F+}	LED Positive Going Threshold Current	0.8	1.7	5.0	mA	V _{CC} = 5 V, I _{OL} = 8.0 mA

Notes:

- Derate LED linearly 1.33 mW/°C above 25° C.
- UL recognition is for 16 kV dc for one minute.
- RMA flux is recommended.
- Derate linearly 1.33 mW/°C above 25° C.
- Measured with input leads shorted together and output leads shorted together in air with a maximum relative humidity of 50 %.







General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics | OPTEK Technology
2900 E. Plano Pkwy, Plano, TX 75074 | Ph: +1 972 323 2200
www.ttelectronics.com | sensors@ttelectronics.com

High Voltage Isolator

OPI1268




General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

dV/dT

OPI1268 dV/dT Emitter



OPI1268 dV/dT Sensor



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.