

## SUMMARY

### # Wires

Low voltage 8



*Image is for illustrative purpose only*

|                  |                                   |
|------------------|-----------------------------------|
| Series           | 3B                                |
| Termination type | Male solder                       |
| IP rating        | 50                                |
| AWG wire size    | 28.00 - 20.00                     |
| Cable Ø          | 0.00 - 0.00 mm                    |
| Status           | active                            |
| Matching parts   | <a href="#">FGJ.3B.308.CLLD11</a> |

### Download

[Request a quote](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

|                   |                                                                                                                               |
|-------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Shell Style/Model | EE*: Fixed receptacle, nut fixing (back panel mounting)                                                                       |
| Keying            | 2 keys (alpha=37.5, plug: female contacts, receptacle: male contacts)                                                         |
| Housing Material  | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Weight            | 27.46 g                                                                                                                       |

### Performance

|               |                           |
|---------------|---------------------------|
| Configuration | 3B.308 : 8 Low Voltage    |
| Insulator     | L: PEEK (UL 94 / V-0/1.5) |
| Rated Current | 13 Amps                   |

### Specifications


Contact Type: Solder  
Contact Dia.: 1.3 mm (0.051in)  
Bucket Dia.: 1 mm (0.039in)  
Max. Solid Conductor: 0.5 mm<sup>2</sup> (AWG 20)  
Max. Stranded Conductor: 0.5 mm<sup>2</sup> (AWG 20)  
R (max): 3.6 mOhm  
Vtest (contact-shell): 1150 V (AC), 1630 V (DC)  
Vtest (contact-contact): 1650 V (AC), 2350 V (DC)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Others

- Endurance (Shell): 5000
- Temp (min / max): -55° C / +250° C
- Humidity (max): <=95% [at 60 deg C / 140 F]
- Vibration: 15 g [10 Hz - 2000 Hz]
- Shock Resistance: 100 g [ 6 ms]
- Climatical Category: 50/175/21
- Shielding (min): 75 dB (10 MHz)
- Shielding (min): 40 dB (1 GHz)
- Salt Spray Corrosion: >1000 hr

DRAWINGS



Dimensions

|     | A    | B    | E    | L    | M    | N    | P    | S1   | S2   | e       |
|-----|------|------|------|------|------|------|------|------|------|---------|
| mm. | 24   | 25   | 6.1  | 30.7 | 4.5  | 28.1 | 12   | 16.5 | 20   | M18x1.0 |
| in. | 0,94 | 0,98 | 0,24 | 1,21 | 0,18 | 1,11 | 0,47 | 0,65 | 0,79 |         |

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cables

|                    |               |        |                                                                                       |
|--------------------|---------------|--------|---------------------------------------------------------------------------------------|
| CMN.08.T20.067PGCE | PVC           | Grey   |    |
| CMN.08.T20.067PGZE |               | Grey   |    |
| CMN.08.T20.067PNZE |               |        |    |
| CMN.08.T22.059QGC  | TPR           | Grey   |                                                                                       |
| CMN.08.T22.059QGZE | TPR (medical) | Grey   |    |
| CMN.08.T26.042QGZE | TPR (medical) | Grey   |    |
| 108220             | PVC           | Black  |    |
| 108240             | PTFE          | White  |    |
| 108260             | PTFE          | White  |    |
| 16080              | PVC           | Grey   |                                                                                       |
| 180240             | PVC           | Black  |    |
| 180260             | PVC           | Black  |    |
| 280250             | PVC           | Grey   |    |
| 335990             | PVC           | Black  |     |
| 335991             | PVC           | Black  |    |
| 380500             | PVC           | Grey   |  |
| 380750             | PVC           | Grey   |  |
| 42265              | PVC           | Yellow |                                                                                       |
| 80140              | PVC           | Grey   |  |
| 8050               | PVC           | Black  |  |
| 8280               | PVC           | Black  |  |

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.