






THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

Customer Drawing



REVISIONS						
REV	ZONE	ECO	DESCRIPTION	DATE	BY	APPR
A	--	--	INITIAL RELEASE	11/22/18	FL	JL
B	--	--	Add LOGO	05/08/19	FL	JL
C	--	--	Remove the gold-plated terminal	05/12/20	JS	JL



- 注(NOTES):
1. 对配公端直径 Mating contact diameter:1.6mm
 2. 额定电流 Current rating: 13A
 3. 端子类型 Terminatin type: Crimp
 4. 压线规格 Wire size: AWG16~18
 - △ 5. 电镀信息 Plating specification:
镍底镀锡 Tin over nickel
 6. 材料规格 Material specification:
6.1. 端子: 铜合金
Contact body: Copper alloy
6.2. 外套: 不锈钢
Outer spring: Stainless steel
 7. 符合ROHS
ROHS compliant

AMPHENOL		Amphenol Technical Products International GZ					
		第三角投影 THIRD ANGLE PROJECTION	页 面 SHEET	幅 面 SIZE	版 次 REV.	比 例 SCALE	PART NAME:
			1 OF 1	A3	C		HC Contact 16#SOCKET AWG16~18
签 名 SIGNATURE		日期 DATE	UNLESS OTHERWISE SPECIFIED				DWG NO:
制 图 DRAWN	JS	05/12/20	1) All dimensions are in metric(mm).				HCTF21504
审 核 CHECKED	YM	05/12/20	2) Tolerances are as follows:				CUST PART #:
批 准 APPROVAL	JL	05/12/20	1 PL DEC ± 1.00				N/A
			2 PL DEC ± 0.50				CUST REV.
			3 PL DEC ± 0.20				-
			Angles $\pm 1^\circ$				