










0.000762 [0.00030] GOLD ON CONTACT AREA, 0.00254-0.00508 [0.00100-.000200]
MATTE TIN ON SOLDER TAIL, ALL OVER 0.00127 [0.00050] NICKEL.



RECOMENDED PCB LAYOUT
FOR USE WITH 0.20 [.008] THICK STENCIL

AZ00119	G=141441				
---------	----------	--	--	--	--

DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±0.13 [.005 4 PLC ±	ANGLES ± FINISH
MATERIAL 4		SEE TABLE	