



Pushing Performance  
Since 1945

## PFT male S- rear 2,5mm²



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 21 03 399 1402  |
| Specification      | PFT male S- rear 2,5mm²   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/21033991402">https://b2b.harting.com/21033991402</a> |

### Identification

|                |                                      |
|----------------|--------------------------------------|
| Category       | Connectors                           |
| Series         | Circular connectors M12              |
| Identification | Power                                |
| Element        | Panel feed through                   |
| Specification  | With conductors<br>for rear mounting |

### Version

|                                   |                           |
|-----------------------------------|---------------------------|
| Gender                            | Male                      |
| Shielding                         | Unshielded                |
| Number of contacts                | 4                         |
| Number of power contacts          | 3                         |
| Number of special contacts        | 1                         |
| Specification of special contacts | PE contact                |
| Coding                            | S-coding                  |
| Locking type                      | Screw locking<br>PushPull |

### Technical characteristics

|                         |         |
|-------------------------|---------|
| Conductor cross-section | 2.5 mm² |
| Conductor cross-section | AWG 14  |
| Rated current           | 12 A    |
| Rated voltage           | 630 V   |
| Rated impulse voltage   | 6 kV    |



**Pushing Performance**  
Since 1945

## Technical characteristics

|  |                             |
|--|-----------------------------|
| Pollution degree                       | 3                           |
| Overvoltage category                   | III                         |
| Insulation resistance                  | >10 <sup>8</sup> Ω          |
| Contact resistance                     | ≤10 mΩ                      |
| Tightening torque                      | 0.8 Nm<br>2 Nm Lock nut     |
| Limiting temperature                   | -40 ... +125 °C             |
| Mating cycles                          | ≥100                        |
| Degree of protection acc. to IEC 60529 | IP65 / IP67 mated condition |
| Isolation group                        | I (600 ≤ CTI)               |
| Conductor length                       | 30 cm                       |

## Material properties

|                                      |  |
|--------------------------------------|--|
| Material (insert)                    | Polyamide (PA)   |
| Material (contacts)                  | Brass  |
| Surface (contacts)                   | Au over Ni Mating side                                 |
| RoHS                                 | compliant with exemption                               |
| RoHS exemptions                      | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                           | compliant with exemption                               |
| China RoHS                           | 50   |
| REACH Annex XVII substances          | Not contained  |
| REACH ANNEX XIV substances           | Not contained  |
| REACH SVHC substances                | Yes  |
| REACH SVHC substances                | Lead   |
| California Proposition 65 substances | Yes  |
| California Proposition 65 substances | Lead   |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08)                                   |
| Requirement set with Hazard Levels   | R26  |

## Specifications and approvals

|                |                                    |
|----------------|------------------------------------|
| Specifications | IEC 61076-2-111<br>IEC 61076-2-010 |
|----------------|------------------------------------|

## Commercial data

|                |   |
|----------------|---|
| Packaging size | 1 |
|----------------|---|



Pushing Performance  
Since 1945

Commercial data

|                                |   |
|--------------------------------|---|
| Net weight                     | 48.9 g  |
| Country of origin              | Romania   |
| European customs tariff number | 85366990  |
| GTIN                           | 5713140227774   |
| eCl@ss                         | 27440103 Sensor-actuator connector chassis (sensor technology actuator) |